

# Manifold MHA1-PR10-3-M3-PI-D25

Part number: 197241

FESTO



 [General operating condition](#)

## Data sheet

| Feature                            | Value                                                                                      |
|------------------------------------|--------------------------------------------------------------------------------------------|
| Max. number of valve positions     | 10                                                                                         |
| Operating pressure                 | 0 bar ... 8 bar                                                                            |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 1 - Low corrosion stress                                                                   |
| LABS (PWIS) conformity             | VDMA24364-B2-L                                                                             |
| Ambient temperature                | -10 °C ... 60 °C                                                                           |
| Mounting method for sub-base       | With through-hole                                                                          |
| Mounting method for valve          | Via female thread                                                                          |
| Pneumatic connection, port 1       | M7                                                                                         |
| Pneumatic connection, port 2       | M3                                                                                         |
| Pneumatic connection, port 3       | M7                                                                                         |
| Material sub-base                  | Wrought aluminium alloy                                                                    |