


Linear drive DLGF-KF-32-200-PPSA

Part number: 5074802

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	32 mm
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	optional
Guide	Recirculating ball bearing guide
Coupling design	Positive-locking (slot)
Position detection	Via proximity switch
Symbol	00991254
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	0 °C ... 60 °C
Cushioning length	11.6 mm
Max. force F _y	1300 N
Max. force -F _z (towards drive)	1600 N
Max. force +F _z (away from drive)	950 N
Max. moment M _x	30 Nm
Max. moment M _y	50 Nm
Max. moment M _z	50 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	483 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	483 N
Moving mass	1290 g
Product weight	4213 g
alternative connections	See product drawing
Type of mounting	With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant Free of copper

Feature	Value
Material cover	Cast aluminium, coated
Material seals	NBR TPE-U(PU)
Material housing	Anodised aluminium