

# Guided drive DFM-6-10-P-A-GF

Part number: 4149945

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	10 mm
Stroke	10 mm
Piston diameter	6 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Max. speed	1.3 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	0.012 J
Max. permissible torque load Mx as a function of stroke	0.008 Nm
Max. effective load dependent upon stroke at defined distance xs	0.85 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	13 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	17 N
Torsional backlash	0.1 deg
Moving mass	9 g
Product weight	33 g
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material cover	High-alloy stainless steel
Material seals	NBR
Material dynamic seals	HNBR
Material end plate	Anodised wrought aluminium alloy
Material guide rod	High-alloy stainless steel

Feature	Value
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel