

Encoder cable NEBM-T1G8-E-20-N-S1G15

Part number: 5105627

FESTO



 General operating condition

Data sheet

Feature	Value
Cable designation	Without inscription label holder
Product weight	1060 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	ITT M3
Electrical connection 1, number of connections/cores	12
Electrical connection 1, used connections/cores	8
Electrical connection 1, connection pattern	00995666
Electrical connection 2, function	Controller side
Electrical connection 2, design	Angular
Electrical connection 2, connection type	Plugs
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	Sub-D
Electrical connection 2, number of connections/cores	15
Electrical connection 2, used connections/cores	8
Electrical connection 2, connection pattern	00995641
Operational voltage range DC	0 V ... 30 V
Nominal operating voltage DC	24 V
Operational voltage range AC	0 V ... 30 V
Nominal operating voltage AC	24 V
Shielding	yes
Cable length	20 m
Cable characteristic	Suitable for energy chains
Bending radius, moving cable	≥48 mm
Cable diameter	5.8 mm
Cable structure	1 x 4 x 0.15 mm ² + 4 x 0.34 mm ²
Nominal cross section conductor	0.34 mm ²
Degree of protection	IP65
Note on degree of protection	IP30 for Sub-D plug connector In assembled state
Ambient temperature	-40 °C ... 80 °C
Ambient temperature with moving cable	-10 °C ... 80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions

Feature	Value
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material cable sheath	TPE-U(PUR)