

# Compact cylinder ADN-S-63-25-I-P-A

Part number: 5132667

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	63 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Piston-rod end	Female thread
Design	Piston Piston rod
Position detection	Via proximity switch
Symbol	00991217
Variants	Piston rod at one end
Operating pressure	0.04 MPa ... 1 MPa
Operating pressure	0.4 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 80 °C
Impact energy in end positions	1.3 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	1750 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	1870 N
Moving mass for 0 mm stroke	151 g
Additional moving mass per 10 mm stroke	16 g
Basic weight for 0 mm stroke	499 g
Additional weight per 10 mm stroke	77 g
Type of mounting	With through-hole Via female thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy
Material dynamic seals	TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel