

# Vacuum generator VN-07-H-T2-PI2-VI2-RI2

Part number: 526103

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature                                       | Value                                     |
|---|---|
| Nominal size, Laval nozzle                    | 0.7 mm                                    |
| Grid dimension                                | 10 mm                                     |
| Mounting position                             | optional                                  |
| Ejector characteristic                        | High vacuum<br>Standard                   |
| Design  | T-shape                                   |
| Symbol  | 00991490                                  |
| Operating pressure for max. suction flow rate | 2.1 bar                                   |
| Operating pressure                            | 1 bar ... 8 bar                           |
| Operating pressure for max. vacuum            | 4.7 bar                                   |
| Max. vacuum                                   | 88 %                                      |
| Nominal operating pressure                    | 6 bar                                     |
| Max. suction flow rate against atmosphere     | 16 l/min                                  |
| Air supply time at nominal operating pressure | 1.9 s                                     |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium            | Lubricated operation not possible         |
| Corrosion resistance class CRC                | 2 - Moderate corrosion stress             |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L                         |
| Media temperature                             | 0 °C ... 60 °C                            |
| Ambient temperature                           | 0 °C ... 60 °C                            |
| Max. tightening torque                        | 0.5 Nm                                    |
| Product weight                                | 13 g                                      |
| Type of mounting                              | With through-hole<br>With accessories     |
| Pneumatic connection, port 1                  | M5  |
| Pneumatic connection, port 3                  | M5  |
| Vacuum connection                             | M5  |
| Material connecting thread                    | Anodised wrought aluminium alloy          |
| Note on materials                             | RoHS-compliant                            |
| Material seals                                | NBR                                       |
| Material receiver nozzle                      | POM                                       |
| Material housing                              | POM-reinforced                            |
| Material transmitter nozzle                   | Wrought aluminium alloy                   |