


Vacuum generator VN-20-L-T6-PI5-VI6-RO2

Part number: 526131

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|---|
| Nominal size, Laval nozzle | 2 mm |
| Grid dimension | 24 mm |
| Silencer design | Open |
| Mounting position | optional |
| Ejector characteristic | High suction rate Standard |
| Integrated function | Open silencer |
| Design | T-shape |
| Symbol | 00991489 |
| Operating pressure for max. suction flow rate | 3 bar |
| Operating pressure | 1 bar ... 8 bar |
| Nominal operating pressure | 6 bar |
| Max. suction flow rate against atmosphere | 188 l/min |
| Air supply time at nominal operating pressure | 0.15 s |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Media temperature | 0 °C ... 60 °C |
| Sound pressure level at nominal operating pressure | 60 dB(A) |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 0.8 Nm |
| Product weight | 183 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | Open silencer |
| Vacuum connection | G3/8 |
| Material connecting thread | Anodised wrought aluminium alloy |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material receiver nozzle | POM |
| Material housing | POM-reinforced |
| Material silencer | Die-cast aluminium POM PU foam |
| Material transmitter nozzle | Wrought aluminium alloy |