

Filter regulator LFR-N1/4-D-5M-O-MIDI-T3-EX4

Part number: 5271800

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Size | Midi |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical +/-5° |
| Grade of filtration | 5 µm |
| Condensate drain | Manually rotating |
| Design | Filter regulator without pressure gauge |
| Max. condensate volume | 42 ml |
| Bowl guard | Integrated as metal bowl |
| Symbol | 00991586 |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | Prepared for G1/4 |
| Operating pressure | 0.1 MPa ... 2 MPa |
| Operating pressure | 1 bar ... 20 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.02 MPa |
| Max. pressure hysteresis | 2.9 psi |
| Standard nominal flow rate (standardised to DIN 1343) | 1600 l/min |
| CE mark (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Gb (GB) |
| Explosion protection | Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX) |
| ATEX category gas | II 2G |
| ATEX category dust | II 2D |
| Explosion ignition protection type for gas | Ex h IIC T6 Gb X |
| Explosion ignition protection type for dust | Ex h IIIC T85°C Db X |
| Explosion ambient temperature | -40°C ≤ Ta ≤ +80°C |
| Operating medium | Inert gas |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 3 - high corrosion stress |

| Feature | Value |
|------------------------------|--|
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -40 °C ... 80 °C |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases |
| Media temperature | -40 °C ... 80 °C |
| Ambient temperature | -40 °C ... 80 °C |
| Product weight | 1400 g |
| Type of mounting | With accessories |
| Pneumatic connection, port 1 | 1/4 NPT |
| Pneumatic connection, port 2 | 1/4 NPT |
| Note on materials | RoHS-compliant |
| Material housing | Die-cast zinc |
| Material bowl | Wrought aluminium alloy |