


# Vacuum generator VN-30-H-T6-PQ4-VQ5-RO2-M

Part number: 532662

FESTO



[General operating condition](#)

## Data sheet

Feature	Value
Nominal size, Laval nozzle	3 mm
Grid dimension	24 mm
Silencer design	Open
Mounting position	optional
Ejector characteristic	Standard High negative pressure
Manual override	Non-detenting
Integrated function	Electric on-off valve Open silencer
Design	T-shape
Symbol	00991492
Valve function	2/2
Operating pressure for max. suction flow rate	3 bar
Operating pressure	2 bar ... 8 bar
Operating pressure for max. vacuum	3.7 bar
Max. vacuum	93 %
Nominal operating pressure	6 bar
Max. suction flow rate against atmosphere	186 l/min
Air supply time at nominal operating pressure	0.13 s
Operational voltage range DC	21.6 V ... 26.4 V
Electrical power consumption	1.2 W
Duty cycle	100%
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Media temperature	0 °C ... 50 °C
Sound pressure level at nominal operating pressure	78 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Product weight	215 g
Electrical connection	Plugs
Type of mounting	With through-hole With accessories
Pneumatic connection, port 1	QS-10

<b>Feature</b>	<b>Value</b>
Pneumatic connection, port 3	Open silencer
Vacuum connection	QS-12
Material connecting thread	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material seals	NBR
Material receiver nozzle	POM
Material housing	PA-reinforced POM-reinforced
Material silencer	Wrought aluminium alloy POM PU foam
Material screws	Steel
Material transmitter nozzle	Wrought aluminium alloy
Material fitting	Brass Nickel-plated