

Quarter turn actuator DAPS-0180-090-R-F0710

Part number: 533421

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Size of valve actuator | 0180 |
| Flange hole pattern | F07 F10 |
| Swivel angle | 90 deg |
| End-position adjustment range at 0° | -1 deg ... 9 deg |
| Shaft connection depth | 24.8 mm |
| Fitting connection conforms to standard | ISO 5211 |
| Cushioning | No cushioning |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Design | Scotch yoke system |
| Position detection | None |
| Closing direction | Closes to the right |
| Symbol | 00991265 |
| Valve connection conforms to standard | VDI/VDE 3845 (NAMUR) |
| Safety Integrity Level (SIL) | up to SIL 2 Low Demand mode |
| Operating pressure | 0.1 MPa ... 0.84 MPa |
| Operating pressure | 1 bar ... 8.4 bar |
| Nominal operating pressure | 0.56 MPa |
| Nominal operating pressure | 5.6 bar |
| Max. swivel frequency at 0.6 MPa (6 bar, 87 psi) | 1 Hz |
| CE mark (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions |
| Explosion protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Certificate issuing authority | German Technical Control Board North (TÜV Nord) 212170801 |
| ATEX category gas | II 2G |
| ATEX category dust | II 2D |
| Explosion ignition protection type for gas | Ex h IIC T6...T3 Gb X |
| Explosion ignition protection type for dust | Ex h IIIC T85°C...T200°C Db X |
| Explosion ambient temperature | -20°C ≤ Ta ≤ +60°C |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 3 - high corrosion stress |

| Feature | Value |
|---|--|
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Torque at nominal operating pressure and 0° swivel angle | 180 Nm |
| Torque at nominal operating pressure and 50° swivel angle | 90 Nm |
| Torque at nominal operating pressure and 90° swivel angle | 135 Nm |
| Note on torque | The operating torque of the actuator must not be higher than the maximum permissible torque listed in ISO 5211, with reference to the size of the mounting flange and of the coupling. |
| Air consumption at 0.6 MPa (6 bar, 87 psi) per cycle 0°-nominal swivel angle-0° | 6.65 l |
| Product weight | 4600 g |
| Shaft connection | T22 |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS compliant |
| Material cover | Wrought aluminium alloy |
| Material seals | Fluoro rubber NBR PUR |
| Material housing | Wrought aluminium alloy |
| Material screws | High-alloy steel |
| Material shaft | High-alloy steel |
| Material number shaft | 1,4305 |