

Motor cable NEBM-M23G15-EH-10-Q9N-R3LEG14

Part number: 5251384

FESTO



 General operating condition

Data sheet

Feature	Value
Based on standard	EN 61984
Cable designation	Without inscription label holder
Product weight	3800 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M23x1
Electrical connection 1, number of connections/cores	15
Electrical connection 1, used connections/cores	12
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00995912
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	RJ45 and open end
Electrical connection 2, number of connections/cores	14
Electrical connection 2, used connections/cores	12
Operational voltage range DC	0 V ... 850 V
Operational voltage range AC	0 V ... 630 V
Current rating at 40° C	17.8 A
Immunity to surge	6 kV
Shielding	yes
Cable length	10 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Test conditions on request
Bending radius, fixed cable	≥51.2 mm
Bending radius, moving cable	≥96 mm
Cable diameter	12.8 mm
Cable diameter tolerance	± 0.3 mm
Cable structure	4 x 1.5 mm ² + 1 x (2 x 0.75 mm ²) + 1 x (2 x 0.24 mm ² + 2 x 2 x 0.15 mm ²)
Nominal cross section conductor	1.5 mm ²
Wire ends	Wire ferrule
Degree of protection	IP67
Note on degree of protection	In assembled state
Ambient temperature	-40 °C ... 90 °C

Feature	Value
Ambient temperature with moving cable	-25 °C ... 80 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material insulating sheath	PP