

# Solenoid valve

## MHP4-M1H-3/2G-1/4

Part number: 525178

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 3/2-way, closed, monostable  |
| Type of actuation                                     | Electric   |
| Construction width                                    | 18 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 400 l/min  |
| pneumatic working port                                | G1/4   |
| Operating voltage                                     | 24V DC   |
| Operating pressure                                    | -0.09 MPa ... 0.8 MPa  |
| Operating pressure                                    | -0.9 bar ... 8 bar   |
| Operating pressure                                    | -13.05 psi ... 116 psi   |
| Design  | Pressure-relieved poppet valve   |
| Type of reset   | Mechanical spring  |
| Degree of protection                                  | IP65   |
| Approval  | c UL us - Recognized (OL)  |
| Nominal size  | 4 mm   |
| Grid dimension  | 24 mm  |
| Note on grid dimension                                | Minimum distance between the valves is 6 mm  |
| Exhaust-air function                                  | With flow control option   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | optional   |
| Manual override                                       | Non-detenting  |
| Type of piloting                                      | Direct   |
| Flow direction  | Reversible with restrictions   |
| Symbol  | 00991308   |
| lap   | Underlap   |
| Operating pressure, reversible                        | -0.09 MPa ... 0.1 MPa  |
| Operating pressure, reversible                        | -0.9 bar ... 1 bar   |
| Operating pressure, reversible                        | -13.05 psi ... 14.5 psi  |
| Max. switching frequency                              | 120 Hz   |
| Switching time off                                    | 5 ms   |
| Switching time on                                     | 10.5 ms  |
| Duty cycle  | 100%   |
| Characteristic coil data                              | 24 V DC: 5.6 W   |
| Permissible voltage fluctuations                      | +/- 10 %   |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |

| <b>Feature</b>  | <b>Value</b>   |
|---|--|
| Vibration resistance                                      | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance  | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                |
| Corrosion resistance class CRC                            | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                                    | VDMA24364-B1/B2-L  |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1   |
| Media temperature   | -5 °C ... 40 °C  |
| Ambient temperature                                       | -5 °C ... 40 °C  |
| Product weight  | 270 g  |
| Electrical connection                                     | Plugs  |
| Type of mounting  | On PR rail   |
| Pneumatic connection, port 1                              | Sub-base   |
| Pneumatic connection, port 2                              | G1/4   |
| Pneumatic connection, port 3                              | Sub-base   |
| Note on materials   | RoHS-compliant   |
| Material seals  | HNBR<br>NBR  |
| Material housing  | Die-cast zinc, coated  |
| Material screws   | Galvanised steel   |