

# Proportional-pressure regulator VPPM-6TA-L-1-F-0L10H-S1

FESTO

Part number: 542219



General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Nominal size, supply                                  | 6 mm   |
| Nominal size, exhaust                                 | 4,5 mm   |
| Type of actuation                                     | Electric   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | optional   |
| Design  | Piloted diaphragm regulator  |
| Short circuit current rating                          | For all electrical connections   |
| Safety instructions                                   | Safety position VPPM: if the power supply cable is interrupted, output pressure is maintained unregulated. |
| Symbol  | 00995303   |
| Reverse polarity protection                           | For all electrical connections   |
| Type of reset   | Mechanical spring  |
| Type of piloting                                      | Pilot actuated   |
| Valve function  | 3-way proportional pressure regulator  |
| Display type  | LED  |
| Pressure regulation range                             | 0.01 MPa ... 1 MPa   |
| Pressure regulation range                             | 0.1 bar ... 10 bar   |
| Inlet pressure 1                                      | 0 bar ... 11 bar   |
| Inlet pressure 1                                      | 0 MPa ... 1.1 MPa  |
| Max. pressure hysteresis                              | 0.05 bar   |
| Standard nominal flow rate (standardised to DIN 1343) | 1400 l/min   |
| Operational voltage range DC                          | 21.6 V ... 26.4 V  |
| Max. current consumption                              | 300 mA   |
| Duty cycle  | 100%   |
| Max. electrical power consumption                     | 7 W  |
| Residual ripple                                       | 10 %   |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]<br>Inert gases   |
| Note on operating and pilot medium                    | Lubricated operation not possible  |
| Approval  | RCM trademark<br>c UL us listed (OL)   |
| KC mark   | KC-EMV   |
| CE mark (see declaration of conformity)               | To EU EMC Directive<br>In accordance with EU RoHS Directive  |
| UKCA marking (see declaration of conformity)          | To UK RoHS instructions  |
| Certificate issuing authority                         | UL E322346   |

| <b>Feature</b>                 | <b>Value</b>                          |
|--------------------------------|---------------------------------------|
| Corrosion resistance class CRC | 2 - Moderate corrosion stress         |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                     |
| Media temperature              | 10 °C ... 50 °C                       |
| Degree of protection           | IP65                                  |
| Ambient temperature            | 0 °C ... 60 °C                        |
| Product weight                 | 400 g                                 |
| Linearity                      | 1 %FS                                 |
| Hysteresis                     | 0.5 %FS                               |
| Reproducibility                | 0.5 %FS                               |
| Total accuracy                 | 1.25%FS                               |
| Temperature coefficient        | 0.04 %/K                              |
| Repetition accuracy FS         | 0.5 %                                 |
| Electrical connection          | Via sub-base                          |
| Type of mounting               | With through-hole<br>With accessories |
| Pneumatic connection, port 1   | Sub-base                              |
| Pneumatic connection, port 2   | Sub-base                              |
| Pneumatic connection, port 3   | Sub-base                              |
| Note on materials              | RoHS-compliant                        |
| Material housing               | Wrought aluminium alloy<br>Anodised   |