

# Mini slide DGSL-12-80-Y3A

Part number: 543980

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Stroke	80 mm
Adjustable end position range/length front	68 mm
Adjustable end position range/length rear	25.5 mm
Piston diameter	16 mm
Operating mode, drive unit	Yoke
Cushioning	Progressive shock absorber at both ends
Mounting position	optional
Guide	Ball bearing cage guide
Design	Yoke Piston Piston rod Slide
Position detection	Via proximity switch
Symbol	00991263
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Max. speed	0.8 m/s
Repetition accuracy	±0.01 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Ambient temperature	0 °C ... 60 °C
Impact energy in end positions	2 J
Cushioning length	10 mm
Max. force F <sub>y</sub>	1280 N
Max. force F <sub>z</sub>	1280 N
Max. moment M <sub>x</sub>	20 Nm
Max. moment M <sub>y</sub>	15 Nm
Max. moment M <sub>z</sub>	15 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	104 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Moving mass	456 g
Product weight	1148 g

<b>Feature</b>	<b>Value</b>
alternative connections	See product drawing
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel