

# Three-point gripper HGDT-40-A-G2

Part number: 540867

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Stroke per gripper jaws	6 mm
Max. replacement accuracy	≤0.2 mm
Max. angular gripper jaw backlash ax, ay	≤0.1 deg
Max. gripper jaw backlash Sz	≤0.05 mm
Rotationally symmetrical	≤0.2 mm
Repetition accuracy, gripper	≤0.03 mm
Number of gripper jaws	3
Mounting position	optional
Mode of operation	Double-acting
Gripper function	3-point
Gripper force back-up	During closing
Design	Wedge-shaped drive Force pilot operated motion sequence
Position detection	Via proximity switch
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Operating pressure of blocked air	0 bar ... 0.5 bar
Max. operating frequency of gripper	≤4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	111 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	87 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	5.23 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	800 N
Max. torque at gripper Mx static	30 Nm
Max. torque at gripper My static	20 Nm
Max. torque at gripper Mz static	25 Nm
Lubrication interval for guide components	5 MioCyc
Max. mass per external gripper finger	70 g
Product weight	837 g

<b>Feature</b>	<b>Value</b>
Type of mounting	Either: Via through-hole and dowel pin Via female thread and dowel pin
Pneumatic connection, blocked air	M5
Pneumatic connection	M5
Material cover cap	High-alloy stainless steel
Material housing	Wrought aluminium alloy Coated with COMPCOTE
Material gripper jaws	Hardened steel