


# Vacuum generator VN-14-L-T4-PI4-VI5-RO2

Part number: 547708

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Nominal size, Laval nozzle	1.4 mm
Grid dimension	18 mm
Silencer design	Open
Mounting position	optional
Ejector characteristic	High suction rate Standard
Integrated function	Open silencer
Design	T-shape
Symbol	00991489
Operating pressure for max. suction flow rate	8 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction flow rate against atmosphere	90 l/min
Air supply time at nominal operating pressure	0.25 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Media temperature	0 °C ... 60 °C
Sound pressure level at nominal operating pressure	77 dB(A)
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	40 g
Type of mounting	With through-hole With accessories
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 3	Open silencer
Vacuum connection	G1/4
Material connecting thread	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material silencer	Die-cast aluminium POM PU foam
Material transmitter nozzle	Wrought aluminium alloy