



Diffuse sensor SOEG-RT-M12-NS-K-2L

Part number: 547906

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Symbol	00991639
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Measured variable	Position
Measuring principle	Optoelectronic
Measurement method	Diffuse sensor
Type of light	Red
Operating distance	70 mm ... 300 mm
Ambient temperature	-25 °C ... 55 °C
Switching output	NPN
Switching element function	Light switching
Hysteresis	≤30 mm
Max. switching frequency	1000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 36 V
Residual ripple	20%
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Electrical connection	Cable
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Material insulating sheath	PVC
Size	M12
Type of mounting	Via lock nut
Tightening torque	10 Nm
Mounting position	optional
Product weight	100 g
Material housing	Chrome-plated
Switching status indication	Yellow LED

Feature	Value
Function reserve indication	Green LED
Setting options	Potentiometer
Setting range lower limit	70 mm
Setting range upper limit	300 mm
Ambient temperature with moving cable	-5 °C ... 55 °C
Degree of protection	IP65 IP67
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III