

# Swivel/linear unit DSL-16-50-270-P-A-S20-B

Part number: 556405

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Rotation angle adjustment range	0 deg ... 270 deg
Stroke	50 mm
Piston diameter	16 mm
Swivel angle	0 deg ... 272 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Fine adjustment	-6 deg
Mode of operation	Double-acting
Design	Vane
Position detection	Via proximity switch
Symbol	00991269
Variants	Through, hollow piston rod
Protection against torque/guide	With plain-bearing guide
Operating pressure	2.5 bar ... 8 bar
Max. impact speed	0.5 m/s
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	2 Hz
Rotary angle backlash	2 deg
Repetition accuracy	1 deg
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Dynamic load torque	0.1 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	73.5 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	102.5 N
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	1.25 Nm
Permissible mass moment of inertia	3.5E-5 kgm <sup>2</sup>
Product weight	860 g
Basic weight for 0 mm stroke	695 g
Additional weight per 10 mm stroke	33 g
Type of mounting	Clamped in T-slot Via male thread
Pneumatic connection	M5

<b>Feature</b>	<b>Value</b>
Material cover	Wrought aluminium alloy Anodised
Material seals	TPE-U(PU)
Material housing	Smooth anodised
Material piston rod	Tempered steel