

Swivel/linear unit DSL-16-40-270-P-A-S20-B

Part number: 556399

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Rotation angle adjustment range | 0 deg ... 270 deg |
| Stroke | 40 mm |
| Piston diameter | 16 mm |
| Swivel angle | 0 deg ... 272 deg |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Fine adjustment | -6 deg |
| Mode of operation | Double-acting |
| Design | Vane |
| Position detection | Via proximity switch |
| Symbol | 00991269 |
| Variants | Through, hollow piston rod |
| Protection against torque/guide | With plain-bearing guide |
| Operating pressure | 2.5 bar ... 8 bar |
| Max. impact speed | 0.5 m/s |
| Max. swivel frequency at 0.6 MPa (6 bar, 87 psi) | 2 Hz |
| Rotary angle backlash | 2 deg |
| Repetition accuracy | 1 deg |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Dynamic load torque | 0.1 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 73.5 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 102.5 N |
| Theoretical torque at 0.6 MPa (6 bar, 87 psi) | 1.25 Nm |
| Permissible mass moment of inertia | 3.5E-5 kgm ² |
| Product weight | 827 g |
| Basic weight for 0 mm stroke | 695 g |
| Additional weight per 10 mm stroke | 33 g |
| Type of mounting | Clamped in T-slot Via male thread |
| Pneumatic connection | M5 |

| Feature | Value |
|---------------------|-------------------------------------|
| Material cover | Wrought aluminium alloy Anodised |
| Material seals | TPE-U(PU) |
| Material housing | Smooth anodised |
| Material piston rod | Tempered steel |