

# Electrical slide EGSK-46-400-10P

Part number: 562786

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Working stroke	400 mm
Size	46
Reversing backlash theoretical	≤20 µm
Spindle diameter	15 mm
Spindle pitch	10 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	With ball screw drive
Referencing	Reference switch
Spindle type	Ball screw drive
Symbol	00991211
Max. acceleration	20 m/s <sup>2</sup>
Max. speed	0.52 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C ... 40 °C
Dynamic basic load rating fixed bearing	6600 N
Dynamic basic load rating linear guide	21747 N
Dynamic basic load rating ball screw	3140 N
2nd moment of area ly	240000 mm <sup>4</sup>
2nd moment of area lz	1500000 mm <sup>4</sup>
Max. drive torque	0.42 Nm
Max. force Fy	4919 N
Max. force Fz	4919 N
Max. moment Mx	145 Nm
Max. moment My	48.7 Nm
Max. moment Mz	48.7 Nm
Max. feed force Fx	264 N
Frictional torque independent of load	0.1 Nm
Static basic load rating ball screw	6760 N
Static basic load rating linear guide	45500 N
Mass moment of inertia JH per metre of stroke	0.39 kgcm <sup>2</sup>
Mass moment of inertia JO	0.0847 kgcm <sup>2</sup>

<b>Feature</b>	<b>Value</b>
Feed constant	10 mm/U
Static basic load rating fixed bearing	3240 N
Reference service life	5000 km
Moving mass	910 g
Weight of slide	910 g
Product weight	10250 g
Weight of additional slide	910 g
Basic weight for 0 mm stroke	5170 g
Additional weight per 10 mm stroke	127 g
Type of mounting	Via female thread and dowel pin
Material end cap	Die-cast aluminium Coated
Material profile	Coated High-alloy steel
Note on materials	RoHS-compliant
Material drive cover	Die-cast aluminium Coated
Material slide	Steel
Material ball screw nut	Steel
Material spindle	Steel