

Pressure sensor SDE3-D10M-B-WQ4-2P-M12

Part number: 568666

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Symbol	00991165
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	1x relative pressure/1x differential pressure
Measurement method	Piezoresistive pressure sensor with display
Start value for pressure measuring range	0 MPa
Start value for pressure measuring range	0 bar
Start value for pressure measuring range	0 psi
End value for pressure measuring range	1 MPa
End value for pressure measuring range	10 bar
End value for pressure measuring range	145 psi
Overload pressure	2 MPa
Overload pressure	20 bar
Overload pressure	290 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Media temperature	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Accuracy in ± % FS	2 %FS ... 3 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature coefficient in ± %FS/K	0.05 %FS/K
Switching output	2xPNP
Switching function	Freely programmable
Switching element function	Switchable
Reproducibility of switching value	0.3 %
Switch-on time	3 ms
Switch-off time	3 ms
Max. output current	100 mA
Voltage drop	1.5 V
Display range start value	0 %FS
Display range end value	100 %FS
Short circuit current rating	yes

Feature	Value
Overload protection	Available
Operational voltage range DC	15 V ... 30 V
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, type of mounting	Screw-type lock Not rotatable
Electrical connection 1, compatible type of mounting	Compatible with rotatable screw-type lock
Electrical connection 1, connection pattern	00997595
Type of mounting	With through-hole With H-rail Via wall/surface bracket
Mounting position	optional
Pneumatic connection	QS-4
Product weight	43 g
Material housing	PA-reinforced
Material in contact with the medium	FPM Nickel-plated brass NBR PA-reinforced
Display type	Illuminated LCD
Displayable units	bar
Switching status indication	LCD yellow
Setting options	Teach-in
Protection against tampering	PIN code
Setting range threshold value	0 % ... 100 %
Setting range hysteresis	0 % ... 90 %
Degree of protection	IP65
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1