

Electrical slide EGSK-26-200-6P

Part number: 562771

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|----------------------------------|
| Working stroke | 200 mm |
| Size | 26 |
| Reversing backlash theoretical | $\leq 20 \mu\text{m}$ |
| Spindle diameter | 8 mm |
| Spindle pitch | 6 mm/U |
| Mounting position | optional |
| Guide | Recirculating ball bearing guide |
| Design | With ball screw drive |
| Referencing | Reference switch |
| Spindle type | Ball screw drive |
| Symbol | 00991211 |
| Max. acceleration | 10 m/s ² |
| Max. speed | 0.59 m/s |
| Repetition accuracy | $\pm 0.01 \text{ mm}$ |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Degree of protection | IP10 |
| Ambient temperature | 0 °C ... 40 °C |
| Dynamic basic load rating fixed bearing | 1380 N |
| Dynamic basic load rating linear guide | 5746 N |
| Dynamic basic load rating ball screw | 1950 N |
| 2nd moment of area ly | 17000 mm ⁴ |
| 2nd moment of area lz | 150000 mm ⁴ |
| Max. drive torque | 0.11 Nm |
| Max. force Fy | 1541 N |
| Max. force Fz | 1541 N |
| Max. moment Mx | 26.2 Nm |
| Max. moment My | 8.9 Nm |
| Max. moment Mz | 8.9 Nm |
| Max. feed force Fx | 116 N |
| Frictional torque independent of load | 0.015 Nm |
| Static basic load rating ball screw | 3510 N |
| Static basic load rating linear guide | 12150 N |
| Mass moment of inertia JH per metre of stroke | 0.0316 kgcm ² |
| Mass moment of inertia JO | 0.00481 kgcm ² |

| Feature | Value |
|--|---------------------------------|
| Feed constant | 6 mm/U |
| Static basic load rating fixed bearing | 1760 N |
| Reference service life | 3000 km |
| Moving mass | 153 g |
| Weight of slide | 153 g |
| Product weight | 1620 g |
| Weight of additional slide | 153 g |
| Basic weight for 0 mm stroke | 780 g |
| Additional weight per 10 mm stroke | 42 g |
| Type of mounting | Via female thread and dowel pin |
| Material end cap | Die-cast aluminium Coated |
| Material profile | High-alloy stainless steel |
| Note on materials | RoHS-compliant |
| Material drive cover | Die-cast aluminium Coated |
| Material slide | Steel |
| Material ball screw nut | Steel |
| Material spindle | Steel |