

# Hinge cylinder DW-80-150-Y-G

Part number: 565797

FESTO



 General operating condition

## Data sheet

Feature	Value
Stroke	150 mm
Piston diameter	80 mm
Piston rod thread	M20x1.5
Broad rod clevis/swivel mounting	28 mm
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Design	Piston Piston rod with rod clevis Swivel mounting on bearing cap Cylinder barrel
Speed regulation	Integrated flow control at both ends
Position detection	Without
Piston-rod end	Male thread with rod clevis
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	1.8 J
Cushioning length	30 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	2721 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	3016 N
Moving mass for 0 mm stroke	1651 g
Additional moving mass per 10 mm stroke	39 g
Basic weight for 0 mm stroke	4185 g
Additional weight per 10 mm stroke	65 g
alternative connections	See product drawing
Type of mounting	Via swivel mounting on bearing cap With accessories
Pneumatic connection	G3/8
Material rod clevis	Cast steel Tempered steel
Note on materials	RoHS-compliant
Material wiper	Bronze

<b>Feature</b>	<b>Value</b>
Material cover	Die-cast aluminium Anodised
Material seals	NBR
Material piston rod	Tempered steel Hard-chrome-plated
Material cylinder barrel	Wrought aluminium alloy Anodised