

Electrical sub-base VAVE-L1-1K6-LR

Part number: 573945

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Cable characteristic | For static applications |
| Reverse polarity protection | Bipolar |
| Additional functions | Spark arresting Holding current reduction |
| Signal status display | LED |
| Nominal operating voltage DC | 24 V |
| Immunity to surge | 0.8 kV |
| Pollution degree | 3 |
| Approval | RCM trademark |
| CE mark (see declaration of conformity) | To EU EMC Directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP65 |
| Ambient temperature | -5 °C ... 60 °C |
| Mounting position | optional |
| Max. tightening torque | 0.27 Nm |
| Min. cable bending radius | 34 mm |
| Product weight | 11 g |
| Electrical connection | Square design/open end |
| Cable structure | 2 x 0.25 mm ² |
| Cable diameter | 3.4 mm |
| Cable diameter tolerance | ± 0.1 mm |
| Cable length | 0.5 m |
| Wire ends | Wire ferrule |
| Protective conductor connection | Not available |
| Type of mounting | On solenoid valve via self-tapping screw |
| Housing colour | Black |
| Note on materials | RoHS-compliant |
| Material cover | PA |
| Material seals | EPDM |
| Material housing | PA |
| Material cable sheath | TPV |
| Material screws | Tempered steel |