

Solenoid valve MHJ10-S-2,5-HF/LP

Part number: 567796

FESTO



 General operating condition

Data sheet

Feature	Value
Valve function	2/2-way, closed, monostable
Type of actuation	Electric
Construction width	10 mm
Standard nominal flow rate (standardised to DIN 1343)	160 l/min
pneumatic working port	Sub-base
Operating voltage	24V DC
Operating pressure	0.05 MPa ... 0.4 MPa
Operating pressure	0.5 bar ... 4 bar
Operating pressure	7.25 psi ... 58 psi
Design	Poppet valve without spring return
Type of reset	Pneumatic spring
Degree of protection	IP55
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Grid dimension	10.5 mm
Note on operation	Do not operate without flow. For block mounting with flow, max. ambient temperature 45°C.
Sealing principle	Hard
Mounting position	optional
Manual override	None
Type of piloting	Direct
Flow direction	Non-reversible
Symbol	00992259
Reverse polarity protection	For operating voltage
Additional functions	Safety shut-off
b value	0.36
C value	0.66 l/sbar
Max. switching frequency	500 Hz
Switching time on 0.4 MPa (4 bar, 58 psi) and 24 V in new condition	1 ms
Switching time off 0.4 MPa (4 bar, 58 psi) and 24 V in new condition	0.5 ms
Switching time on 0.05 MPa (0.5 bar, 7.25 psi) and 24 V in new condition	0.8 ms
Switching time off 0.05 MPa (0.5 bar, 7.25 psi) and 24 V in new condition	0.6 ms
Tolerance switching time off	+15%/-25%
Tolerance switching time on	+/-15%

Feature	Value
Operational voltage range DC	21.6 V ... 26.4 V
Input resistance	34 kOhm
Duty cycle	100%
Characteristic coil data	24 V DC: low-current phase 2.0 W, high-current phase 7.0 W
Trigger signal voltage range DC	3 V ... 30 V
Note on input current	0.09-0.44 mA with a trigger signal of 3-15 V 0.44-15.44 mA with a trigger signal of 15-30 V
Permissible voltage fluctuations	+/- 10 %
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Restrictions for environmental and media temperature	As a function of switching frequency (see graph)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 50 °C
Permissible solenoid surface temperature	120 °C
Media temperature	-5 °C ... 60 °C
Ambient temperature	-5 °C ... 60 °C
Max. tightening torque for valve mounting	0.7 Nm
Product weight	75 g
Electrical connection	Cable
Cable length	2.5 m
Type of mounting	On sub-base
Pneumatic connection, port 1	Sub-base
Pneumatic connection, port 2	Sub-base
Note on materials	RoHS-compliant
Material seals	HNBR
Material housing	PPS reinforced
Material cable sheath	PUR
Material screws	Steel