

Quarter turn actuator DAPS-0106-090-R-F0507-MW-T6

Part number: 8005014

FESTO



 General operating condition

Data sheet

Feature	Value
Size of valve actuator	0106
Flange hole pattern	F05 F07
Swivel angle	92 deg
Shaft connection depth	19.3 mm
Fitting connection conforms to standard	ISO 5211
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Double-acting
Design	Scotch yoke system
Position detection	None
Closing direction	Closes to the right
Symbol	00991265
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)
Safety Integrity Level (SIL)	up to SIL 2 high demand mode up to SIL 2 Low Demand mode
Operating pressure	0.3 MPa ... 0.84 MPa
Operating pressure	3 bar ... 8.4 bar
Nominal operating pressure	0.56 MPa
Nominal operating pressure	5.6 bar
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Certificate issuing authority	German Technical Control Board North (TÜV Nord) 212170801
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T6...T3 Gb X
Explosion ignition protection type for dust	Ex h IIIC T85°C...T200°C Db X
Explosion ambient temperature	-50°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress

Feature	Value
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-50 °C ... 60 °C
Torque at nominal operating pressure and 0° swivel angle	106 Nm
Torque at nominal operating pressure and 50° swivel angle	53 Nm
Torque at nominal operating pressure and 90° swivel angle	80 Nm
Air consumption at 0.6 MPa (6 bar, 87 psi) per cycle 0°-nominal swivel angle-0°	3.85 l
Product weight	4000 g
Shaft connection	T17
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	FVMQ PTFE-reinforced
Material housing	Wrought aluminium alloy
Material screws	High-alloy steel
Material shaft	High-alloy steel
Material number shaft	1,4305