

# Proportional-pressure regulator VPPM-6L-L-1-G18-0L2H-LK-S1

Part number: 8024258

FESTO



General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Nominal size, supply                                  | 6 mm   |
| Nominal size, exhaust                                 | 4,5 mm   |
| Type of actuation                                     | Electric   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | optional   |
| Design  | Piloted diaphragm regulator  |
| Short circuit current rating                          | For all electrical connections   |
| Safety instructions                                   | Safety position VPPM: if the power supply cable is interrupted, output pressure is maintained unregulated. |
| Symbol  | 00995303   |
| Reverse polarity protection                           | For all electrical connections   |
| Type of reset   | Mechanical spring  |
| Type of piloting                                      | Pilot actuated   |
| Valve function  | 3-way proportional pressure regulator  |
| Display type  | LED  |
| Pressure regulation range                             | 0.002 MPa ... 0.2 MPa  |
| Pressure regulation range                             | 0.02 bar ... 2 bar   |
| Inlet pressure 1                                      | 0 bar ... 4 bar  |
| Inlet pressure 1                                      | 0 MPa ... 0.4 MPa  |
| Max. pressure hysteresis                              | 0.01 bar   |
| Standard nominal flow rate (standardised to DIN 1343) | 380 l/min  |
| Operational voltage range DC                          | 18 V ... 30 V  |
| Max. current consumption                              | 300 mA   |
| Duty cycle  | 100%   |
| Max. electrical power consumption                     | 7 W  |
| Protocol  | I-Port<br>IO-Link®   |
| Residual ripple                                       | 10 %   |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]<br>Inert gas   |
| Note on operating and pilot medium                    | Lubricated operation not possible  |
| Approval  | RCM trademark<br>c UL us listed (OL)   |
| KC mark   | KC-EMV   |
| CE mark (see declaration of conformity)               | To EU EMC Directive<br>In accordance with EU RoHS Directive  |

| Feature                                      | Value  |
|--|--|
| UKCA marking (see declaration of conformity) | To UK RoHS instructions                        |
| Certificate issuing authority                | UL E322346                                     |
| Corrosion resistance class CRC               | 2 - Moderate corrosion stress                  |
| LABS (PWIS) conformity                       | VDMA24364-B1/B2-L                              |
| Media temperature                            | 10 °C ... 50 °C                                |
| Degree of protection                         | IP65   |
| Ambient temperature                          | 0 °C ... 60 °C                                 |
| Product weight                               | 400 g  |
| Linearity                                    | 1 %FS  |
| Hysteresis                                   | 0.5 %FS  |
| Reproducibility                              | 0.5 %FS  |
| Total accuracy                               | 1.25%FS  |
| Temperature coefficient                      | 0.04 %/K                                       |
| Repetition accuracy FS                       | 0.5 %  |
| IO-Link, Protocol version                    | Device V 1.1                                   |
| IO-Link, communication mode                  | COM1 (4.8 kB), COM2 (38.4 kB), COM3 (230.4 kB) |
| IO-Link, Port class                          | A  |
| IO-Link, Process data length OUT             | 2 bytes  |
| IO-Link, Process data length IN              | 2 bytes  |
| IO-Link, Min. cycle time                     | 0.5 ms   |
| Type of mounting                             | With through-hole<br>With accessories          |
| Pneumatic connection, port 1                 | G1/8   |
| Pneumatic connection, port 2                 | G1/8   |
| Pneumatic connection, port 3                 | G1/8   |
| Note on materials                            | RoHS-compliant                                 |
| Material housing                             | Wrought aluminium alloy<br>Anodised            |