

Solenoid coil

VACN-N-K11-16B-0.5-U4-M

FESTO

Part number: 8029145



 General operating condition

Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Duty cycle	100%
Insulation material class	H
Insulation material class of enamelled wire	H
Characteristic coil data	120 V AC: 60 Hz, pick-up power 10.0 VA, holding power 6.8 VA
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
Explosion protection certification outside the EU	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III, Div. 1 (CA) Class III, Div. 1 (US) EPL Gb (US)
Explosion protection	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III, Div. 1 (CA) Class III, Div. 1 (US) Zone 1 (US)
Certificate issuing authority	CSA 265489 DNV TAA000011J FM 3053936
Explosion ignition protection type for gas	AEx m II T4 Ex m II T4
Explosion ambient temperature	-20°C ≤ Ta ≤ +60°C
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	207 g
Electrical connection	Cable
Cable length	0.61 m
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material housing	Polymer Steel

Feature	Value
Material winding	Copper