


# Stem actuated valve VMEF-SCZ-M52-E-N18

FESTO

Part number: 8031326



[PDF General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 5/2-way, monostable  |
| Type of actuation                                     | Mechanical   |
| Construction width                                    | 20 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 750 l/min  |
| pneumatic working port                                | 1/8 NPT  |
| Operating pressure                                    | -0.095 MPa ... 1 MPa   |
| Operating pressure                                    | -0.95 bar ... 10 bar   |
| Design  | Piston gate valve  |
| Type of reset   | Pneumatic spring   |
| Nominal size  | 5.2 mm   |
| Instructions on use                                   | Do not use as a mechanical stop  |
| Sealing principle                                     | Soft   |
| Mounting position                                     | optional   |
| Type of piloting                                      | Pilot actuated   |
| Pilot air supply                                      | External   |
| Flow direction  | Reversible   |
| Symbol  | 00992221   |
| lap   | Overlap  |
| Pilot pressure  | 0.25 MPa ... 1 MPa   |
| Pilot pressure  | 2.5 bar ... 10 bar   |
| Pilot pressure  | 36.25 psi ... 145 psi  |
| Max. switching frequency                              | 3 Hz   |
| Explosion protection                                  | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX)                         |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:-:-]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L  |
| Media temperature                                     | -10 °C ... 60 °C   |
| Ambient temperature                                   | -10 °C ... 60 °C   |
| Actuating force                                       | 14 N   |
| Product weight  | 150 g  |
| Type of mounting                                      | With through-hole  |
| Pilot air port 12/14                                  | M5   |

| <b>Feature</b>               | <b>Value</b>                     |
|------------------------------|----------------------------------|
| Pneumatic connection, port 1 | 1/8 NPT                          |
| Pneumatic connection, port 2 | 1/8 NPT                          |
| Pneumatic connection, port 3 | 1/8 NPT                          |
| Pneumatic connection, port 4 | 1/8 NPT                          |
| Pneumatic connection, port 5 | 1/8 NPT                          |
| Note on materials            | RoHS-compliant                   |
| Material cover               | PA-reinforced                    |
| Material seals               | NBR                              |
| Material housing             | Anodised wrought aluminium alloy |