

Mini slide DGST-10-10-E1A

Part number: 8078839

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	10 mm
Operating mode, drive unit	Yoke
Cushioning	Elastomer cushioning, double-sided, stroke not adjustable
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Yoke Piston rod Slide
Position detection	Via proximity switch
Symbol	00991249
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Max. speed	0.5 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	0.05 J
Cushioning length	1.6 mm
Max. force F _y	470 N
Max. force F _z	470 N
Max. moment M _x	3 Nm
Max. moment M _y	3 Nm
Max. moment M _z	3 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	79 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	94 N
Moving mass	124 g
Product weight	247 g

Feature	Value
Type of mounting	With through-hole
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material guide	POM TPE-E High-alloy steel
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel