

Shock absorber DYSS-G8-5-5-Y1F

Part number: 8073914

FESTO



 General operating condition

Data sheet

| Feature | Value |
|----------------------------------------|-------------------------------|
| Size | 5 |
| Stroke | 5 mm |
| Cushioning | Self-adjusting |
| Mounting position | optional |
| Position detection | Without |
| Symbol | 00991495 |
| Max. impact speed | 1 m/s |
| Reset time at room temperature | 0.2 s |
| Reset time at min. ambient temperature | 1 s |
| Mode of operation | Pushing Single-acting |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Cushioning length | 5 mm |
| Max. stop force | 200 N |
| Max. tightening torque | 2 Nm |
| Max. energy consumption per stroke | 1.4 J |
| Max. energy consumption per hour | 8000 J |
| Max. residual energy | 0.01 J |
| Reset force | 0.9 N |
| Min. insertion force | 10 N |
| Product weight | 16 g |
| Load range | 2.5 kg |
| Type of mounting | Via threaded sleeve |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material housing | High-alloy steel |
| Material piston rod | High-alloy steel |