

Cantilever axis ELCC-TB-KF-110-1700-0H-P0-CR

Part number: 8082417

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Effective diameter of drive pinion	68.755 mm
Working stroke	1700 mm
Size	110
Stroke reserve	0 mm
Toothed-belt pitch	8 mm
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical cantilever axis
Symbol	00991210
Max. acceleration	30 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0.05 mm
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C ... 60 °C
2nd moment of area I _y	6830570 mm ⁴
2nd moment of area I _z	4925970 mm ⁴
Max. drive torque	90 Nm
Max. force F _y	20596 N
Max. force F _z	20022 N
Max. moment M _x	317 Nm
Max. moment M _y	2368 Nm
Max. moment M _z	2286 Nm
Max. feed force F _x	2500 N
Mass moment of inertia J _H per metre of stroke	174.9 kgcm ²
Mass moment of inertia J _L per kg of working load	11.8 kgcm ²
Mass moment of inertia J _O	157.1 kgcm ²
Feed constant	216 mm/U
Reference service life	5000 km
Lubrication interval dependent on operating distance	1000 km
Moving mass for 0 mm stroke	10017 g
Additional moving mass per 10 mm stroke	148 g
Basic weight for 0 mm stroke	27299 g
Additional weight per 10 mm stroke	148 g
Material end cap	Anodised wrought aluminium alloy

Feature	Value
Material profile	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material drive head	Anodised wrought aluminium alloy
Material guide rail	Rolled steel, Corrotect coated
Material housing	High-alloy stainless steel
Material slide	Anodised die-cast aluminium
Material toothed belt clamping piece	Anodised wrought aluminium alloy
Material toothed belt	Polychloroprene with glass filament and nylon coating