


# Ball screw axis unit ELGS-BS-KF-60-100-12P-ST-M-H1-PLK-AA

FESTO

Part number: 8083383



[PDF](#) General operating condition

## Data sheet

| Feature  | Value   |
|--|---|
| Working stroke                                     | 100 mm  |
| Size   | 60  |
| Stroke reserve                                     | 0 mm  |
| Spindle diameter                                   | 12 mm   |
| Spindle pitch                                      | 12 mm/U   |
| Mounting position                                  | optional  |
| Guide  | Recirculating ball bearing guide  |
| Design   | Electromechanical linear axis<br>With ball screw<br>With integrated drive                               |
| Type of motor                                      | Stepper motor   |
| Spindle type                                       | Ball screw drive  |
| Symbol   | 00997292  |
| Position detection                                 | Motor encoder<br>Via proximity switch   |
| Referencing  | Positive fixed stop block<br>Negative fixed stop block  |
| Rotor position sensor                              | Absolute single-turn encoder  |
| Rotor position sensor, encoder measuring principle | Magnetic  |
| Temperature monitoring                             | Switch-off for excessive temperature<br>Integrated precise CMOS temperature sensor with analogue output |
| Additional functions                               | User interface<br>Integrated end-position sensing   |
| Display  | LED   |
| Ready status indication                            | LED   |
| Max. acceleration                                  | 5 m/s <sup>2</sup>  |
| Max. speed   | 0.25 m/s  |
| Speed "Speed press"                                | 0.01 m/s  |
| Repetition accuracy                                | ±0.01 mm  |
| Features of digital logic outputs                  | Configurable<br>Not galvanically isolated   |
| Duty cycle   | 100%  |
| Insulation protection class                        | B   |
| Max. current digital logic outputs                 | 100 mA  |
| Max. current consumption                           | 5300 mA   |
| Max. current consumption, logic                    | 0.3 A   |
| Nominal voltage DC                                 | 24 V  |
| Nominal current                                    | 5.3 A   |

| Feature   | Value  |
|---|--|
| Parameterisation interface  | IO-Link<br>User interface  |
| Rotor position transducer resolution                              | 16 bit   |
| Permissible voltage fluctuations                                  | +/- 15%  |
| Power supply, connection type                                     | Plugs  |
| power supply, connection system                                   | M12x1, T-coded according to EN 61076-2-111                                       |
| Power supply, number of pins/wires                                | 4  |
| Power supply, connection pattern                                  | 00995989   |
| Approval  | RCM trademark  |
| KC mark   | KC-EMV   |
| CE mark (see declaration of conformity)                           | To EU EMC Directive<br>In accordance with EU RoHS Directive                      |
| UKCA marking (see declaration of conformity)                      | To UK instructions for EMC<br>To UK RoHS instructions                            |
| Vibration resistance  | Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance  | Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27                |
| LABS (PWIS) conformity  | VDMA24364 zone III   |
| Cleanroom suitability, measured according to ISO 14644-14         | Class 7 according to ISO 14644-1   |
| Storage temperature   | -20 °C ... 60 °C   |
| Relative air humidity   | 0 - 90%  |
| Degree of protection  | IP40   |
| Protection class  | III  |
| Ambient temperature   | 0 °C ... 50 °C   |
| Note on ambient temperature                                       | Power must be reduced by 2% per K at ambient temperatures above 30°C.            |
| 2nd moment of area Iy   | 441000 mm <sup>4</sup>   |
| 2nd moment of area Iz   | 542000 mm <sup>4</sup>   |
| Max. force Fy   | 3641 N   |
| Max. force Fz   | 3641 N   |
| Max. force Fy total axis  | 600 N  |
| Max. force Fz total axis  | 1800 N   |
| Fy at theoretical life value of 100 km (only guide consideration) | 13400 N  |
| Fz at theoretical life value of 100 km (only guide consideration) | 13400 N  |
| Max. moment Mx  | 29.1 Nm  |
| Max. moment My  | 31.8 Nm  |
| Max. moment Mz  | 31.8 Nm  |
| Max. moment Mx total axis   | 29.1 Nm  |
| Max. moment My total axis   | 31.8 Nm  |
| Max. moment Mz total axis   | 31.8 Nm  |
| Mx at theoretical life value of 100 km (only guide consideration) | 107 Nm   |
| My at theoretical life value of 100 km (only guide consideration) | 117 Nm   |
| Mz at theoretical life value of 100 km (only guide consideration) | 117 Nm   |
| Max. feed force Fx  | 200 N  |
| Reference value effective load, horizontal                        | 20 kg  |
| Reference value effective load, vertical                          | 13 kg  |
| Torsional mass moment of inertia It                               | 29800 mm <sup>4</sup>  |
| Feed constant   | 12 mm/U  |
| Reference service life  | 5000 km  |
| Maintenance interval  | Life-time lubrication  |
| Moving mass   | 525 g  |
| Product weight  | 3372 g   |
| Dynamic deflection (moving load)                                  | 0.05% of the axis length, max. 0.5 mm  |
| Static deflection (load in standstill)                            | 0.1% of the axis length  |

| Feature                                 | Value   |
|---|---|
| Number of digital logic outputs 24 V DC | 2   |
| Number of digital logic inputs          | 2   |
| Specification logic input               | Based on IEC 61131-2, type 1  |
| Working range of logic input            | 24 V  |
| IO-Link, SIO-Mode support               | Yes   |
| Features of logic input                 | Configurable<br>Not galvanically isolated   |
| IO-Link, Protocol version               | Device V 1.1  |
| IO-Link, communication mode             | COM3 (230.4 kBaud)  |
| IO-Link, Port class                     | A   |
| IO-Link, Number of ports                | 1   |
| IO-Link, Process data length OUT        | 2 bytes   |
| IO-Link, Process data content OUT       | Move in 1 bit<br>Move out 1 bit<br>Quit Error 1 bit<br>Move intermediate 1 bit                          |
| IO-Link, Process data length IN         | 2 bytes   |
| IO-Link, Process data content IN        | State Device 1 bit<br>State In 1 bit<br>State Intermediate 1 bit<br>State Move 1 bit<br>State Out 1 bit |
| IO-Link, Service data IN                | 32-bit force<br>32-bit position<br>32-bit speed   |
| IO-Link, Min. cycle time                | 1 ms  |
| IO-Link, Data storage required          | 500 Byte  |
| Max. cable length                       | 15 m outputs<br>15 m inputs<br>20 m with IO-Link® operation   |
| Switching logic for outputs             | PNP (positive switching)  |
| Switching logic for inputs              | PNP (positive switching)  |
| IO-Link, connection technology          | Plugs   |
| Logic interface, connection type        | Plug  |
| Logic interface, connection technology  | M12x1, A-coded according to EN 61076-2-101  |
| Logic interface, number of pins/wires   | 8   |
| Logic interface, plug pattern           | 00992264  |
| Type of mounting                        | Via female thread<br>Via centring sleeve and pin<br>With accessories                                    |
| Material end cap                        | Painted die cast aluminium  |
| Material profile                        | Anodised wrought aluminium alloy  |
| Note on materials                       | RoHS-compliant  |
| Material cover tape                     | High-alloy stainless steel  |
| Material drive cover                    | Painted die cast aluminium  |
| Material guide slide                    | Steel   |
| Material guide rail                     | Steel   |
| Material slide                          | Die-cast aluminium  |
| Material ball screw nut                 | Steel   |
| Material spindle                        | Steel   |