


Air gap sensor SOPA-CM3H-R1-HQ6-PNLK-A-M12

Part number: 8093823

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Symbol	00997316
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC mark	KC-EMV
Note on materials	RoHS-compliant
Detected variable	Distance
Measuring principle	Pneumatic
Sensing range	20 µm ... 200 µm
Operating pressure	4 bar ... 7 bar
Supply pressure	0.8 bar ... 1.6 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature	0 °C ... 50 °C
Repetition accuracy in ± µm	2.5 µm
Switching output	PNP/NPN, switchable
Switching function	Window comparator Threshold value with variable hysteresis
Switching element function	N/C or N/O contact, switchable
Max. output current	100 mA
Analogue output	4 - 20 mA
Starting value of distance characteristic	0 µm
End value of distance characteristic	300 µm
Rise time	22 ms
Max. load resistance current output	500 Ohm
Short circuit current rating	yes
Protocol	IO-Link®
IO-Link, Protocol version	Device V 1.1
IO-Link, Profile	Smart sensor profile
IO-Link, Function classes	Process data variable (PDV) Identification Diagnostics Teach channel Switching signal channel (SSC)

Feature	Value
IO-Link, communication mode	COM2 (38.4 kBaud)
IO-Link, SIO-Mode support	Yes
IO-Link, Port class	A
IO-Link, Process data length OUT	0 bytes
IO-Link, Process data length IN	2 bytes
IO-Link, Process data content IN	1-bit SSC (supply pressure monitoring) 10-bit PDV (distance) 2-bit SSC (distance monitoring)
IO-Link, Service data IN	14-bit supply pressure
IO-Link, Min. cycle time	3 ms
IO-Link, Data storage required	<500 Byte
Operational voltage range DC	22.8 V ... 26.4 V
Max. current consumption	610 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, type of mounting	Not rotatable
Electrical connection 1, compatible type of mounting	Compatible with rotatable screw-type lock
Electrical connection 1, connection pattern	00991172
Type of mounting	With through-hole With H-rail
Pneumatic connection	QS-6
Product weight	630 g
Material housing	PA-reinforced
Display type	Illuminated LCD, multi-colour
Setting options	IO-Link® Teach-in Via display and keys
Protection against tampering	Electronic interlock
Degree of protection	IP65
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L