

Filter regulator MS6-LFR-1/2-D6-E-P-M-AG-MPA-B

Part number: 8098307

FESTO



General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | 6 |
| Series | MS |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical +/-5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manual, rotating |
| Design | Directly actuated piston regulator |
| Max. condensate volume | 27.3 ml |
| Controller function | Output pressure constant With secondary exhausting With return flow function |
| Degree of condensate separation | >75 % |
| Symbol | 00991589 |
| Displayable units | MPa |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | With pressure gauge |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Pressure regulation range | 0.3 bar ... 7 bar |
| Max. pressure hysteresis | 0.035 MPa |
| Max. pressure hysteresis | 0.35 bar |
| Max. pressure hysteresis | 5.075 psi |
| Standard nominal flow rate (standardised to DIN 1343) | 5300 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas |
| Note on operating and pilot medium | Compatibility with ester oil not guaranteed |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 7 according to ISO 14644-1 |
| Storage temperature | -5 °C ... 50 °C |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Media temperature | -5 °C ... 50 °C |
| Ambient temperature | -5 °C ... 50 °C |
| Pore size | 40 µm |
| Product weight | 581 g |
| Type of mounting | With accessories |

| Feature | Value |
|------------------------------|--------------------------------------|
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | G1/2 |
| Note on materials | RoHS compliant |
| Material seals | NBR |
| Material rotary knob | POM |
| Material spring | High-alloy steel Galvanised steel |
| Material filter | Packaging unit |
| Material housing | Reinforced PA |
| Material bowl | Makrolon® |
| Material valve stem | POM |