

Electronics module VMPA14-FB-EMG-8-S

Part number: 8108547



 [General operating condition](#)

Data sheet

Feature	Value
Diagnosis	Undervoltage of valves
Max. number of valve positions	4
Max. number of valve coils	7
Parameterisation	Fail-safe per channel Forcing per channel Idle mode per channel Monitoring
Reverse polarity protection	yes
Operating voltage range DC electronics/sensors	18 V ... 30 V
Operating voltage DC load voltage	18 V ... 30 V
Internal current consumption, load voltage	6.5 mA
Internal current consumption, operating voltage	17 mA
Max. number of outputs	7
Max. number of inputs	1
Nominal pick-up current per solenoid coil	58 mA up to 24 ms
Nominal current with current reduction	25 mA after 24 ms
Isolation channel - internal bus	yes
Corrosion resistance class CRC	(when installed)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-5 °C ... 50 °C
Product weight	30 g
Electrical control	Fieldbus
Material housing	POM
Note on materials	RoHS-compliant