

Parallel gripper DHPC-6-A-NO-S-1

Part number: 8116742

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	6
Stroke per gripper jaws	2 mm
Max. replacement accuracy	0.2 mm
Max. angular gripper jaw backlash ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotationally symmetrical	≤0.2 mm
Repetition accuracy, gripper	≤0.02 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Single-acting Open
Gripper function	Parallel
Gripper force back-up	During opening
Design	Connection direction at side Lever Side mounting method for gripper fingers Force pilot operated motion sequence
Guide	Ball guide
Position detection	Via proximity switch
Symbol	00997349
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Operating pressure	0.35 MPa ... 0.8 MPa
Operating pressure	3.5 bar ... 8 bar
Operating pressure	50.75 psi ... 116 psi
Max. operating frequency of gripper	3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	8 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	6 ms
Max. mass per external gripper finger	6 g
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L

Feature	Value
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C ... 60 °C
Total gripping force, closing, 0.6MPa (6bar, 87 psi)	7.8 N
Gripper force per gripper jaw, closing, 0.6 MPa (6 bar, 87 psi)	3.9 N
Mass moment of inertia	0.012 kgcm ²
Max. force on gripper jaw Fz static	22 N
Max. torque at gripper Mx static	0.24 Nm
Max. torque at gripper My static	0.11 Nm
Max. torque at gripper Mz static	0.11 Nm
Product weight	27 g
Type of mounting	Either: Direct mounting via through-hole Direct mounting via thread
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material housing	Anodised aluminium
Material gripper jaws	High-alloy stainless steel