

Control system CMCB-D1-CC-S0

Part number: 8118456

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Instructions on use | The product is suitable for industrial purposes only. Measures to eliminate radio interference may be required in residential areas. |
| Design | Control cabinet |
| Performance Level (PL) | Category B, Performance Level b |
| Dimensions (W x L x H) | 220 mm x 350 mm x 440 mm |
| Fuse protection (short circuit) | Internal electronic fuse |
| Max. current consumption | 1100 mA |
| Current consumption of the secondary circuit | 5 A |
| Max. power supply | 6 A |
| Nominal operating voltage AC | 230 V |
| Mains types | TT TN IT |
| Mains frequency | 50 Hz ... 60 Hz |
| Pollution degree | 2 |
| CE mark (see declaration of conformity) | To EU EMC Directive To EU Low Voltage Directive |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -20 °C ... 60 °C |
| Relative air humidity | Max. 50% at 40°C |
| Protection against direct and indirect contact | PELV Earthing of all exposed conductive parts |
| Degree of protection | IP54 |
| Environmental conditions | Interior |
| Ambient temperature | 5 °C ... 40 °C |
| Nominal altitude of use | 1000 m NN |
| Product weight | 15000 g |
| Electrical connection | Push-in |
| Note on materials | RoHS-compliant |