

Limit switch box SRBC-CA4-YR90-MW-22A-1W-C2

Part number: 8137094

FESTO



 General operating condition

Data sheet

Feature	Value
Approval	c CSA us (OL)
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
Certificate issuing authority	Eurocert. SIL202587141
Note on materials	RoHS-compliant
Safety Integrity Level (SIL)	Safety Integrity Level 3
Measuring principle	Mechanical/electrical
Ambient temperature	-20 °C ... 80 °C
Switching output	Contacting
Switching element function	Toggle switch, single-pole
Max. output current AC	3000 mA
Max. output current DC	3000 mA
Operational voltage range AC	0 V ... 230 V
Operational voltage range DC	0 V ... 30 V
Microswitch type	Omron SS-5
Electrical connection	Screw terminal
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	Spring-loaded terminal
Electrical connection 1, number of connections/cores	10
Connectable nominal cross section conductor	0.25 mm ² ... 2.5 mm ²
Permissible cable diameter	5 mm ... 13 mm
Dimensions (W x L x H)	127 mm x 98 mm x 122 mm
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1 VDI/VDE 3845 size AA 2 VDI/VDE 3845 size AA 3
Mounting position	optional
Product weight	800 g
Housing colour	grey
Material housing	Die-cast aluminium
Material seals	NBR
Material shaft	High-alloy stainless steel
Material screws	High-alloy stainless steel
Material mounting bracket	High-alloy stainless steel
Material snap ring	High-alloy stainless steel

Feature	Value
Material disc	High-alloy stainless steel
Material cover cap	PC
Position indicator	Yellow/red
Setting range of angular detection	0 deg ... 90 deg
Storage temperature	-20 °C ... 50 °C
Degree of protection	IP66 IP67 NEMA 4/4X
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pollution degree	3