

Compact cylinder ADN-32-70-A-PPS-A

Part number: 8179022

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	70 mm
Piston diameter	32 mm
Piston rod thread	M10x1.25
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Conforms to standard	ISO 21287
Piston-rod end	Male thread
Position detection	Via proximity switch
Symbol	00992970
Variants	Piston rod at one end
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	1 J
Cushioning length	4 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	415 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	483 N
Moving mass	147 g
Product weight	478 g
Type of mounting	With through-hole With female thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material collar screws	Steel
Material cover	Anodised wrought aluminium alloy
Material seals	TPE-U(PUR)
Material piston rod	High-alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy