

Compact cylinder ADN-S-50-20-I-P-A-F1A

Part number: 8142900

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 20 mm |
| Piston diameter | 50 mm |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Mode of operation | Double-acting |
| Piston-rod end | Female thread |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Symbol | 00991217 |
| Variants | Piston rod at one end |
| Operating pressure | 0.04 MPa ... 1 MPa |
| Operating pressure | 0.4 bar ... 10 bar |
| Operating pressure | 5.8 psi ... 145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 5 according to ISO 14644-1 |
| Ambient temperature | 0 °C ... 80 °C |
| Impact energy in end positions | 1 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 1057 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1178 N |
| Moving mass for 0 mm stroke | 104 g |
| Additional moving mass per 10 mm stroke | 16 g |
| Basic weight for 0 mm stroke | 324 g |
| Additional weight per 10 mm stroke | 63 g |
| Type of mounting | With through-hole Via female thread |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Material cover | Anodised wrought aluminium alloy |
| Material dynamic seals | TPE-U(PU) |
| Material housing | Anodised wrought aluminium alloy |

| Feature | Value |
|---------------------|----------------------------|
| Material piston rod | High-alloy stainless steel |