

Shock absorber retainer DADP-ES-G8-25

Part number: 8159237

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------|--------------------------------------|
| Size | 25 |
| Mounting position | optional |
| Design | Stop lever |
| Max. impact speed | 0.8 m/s |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-C1-L |
| Ambient temperature | 0 °C ... 60 °C |
| Max. stop force | 1100 N |
| Max. tightening torque | 8.4 Nm |
| Tolerance for tightening torque | ± 20 % |
| Product weight | 503 g |
| Type of mounting | Via through-hole and centring sleeve |
| Note on materials | RoHS-compliant |
| Material lever | Wrought aluminium alloy |
| Material screws | Galvanised steel |