


Sub-base kit DADP-SP-G9-6-R

Part number: 8173532

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | 6 |
| Mounting position | optional |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-C1-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -10 °C ... 60 °C |
| Max. stop force | 60 N |
| Max. tightening torque | 0.3 Nm |
| Tolerance for tightening torque | ± 15 % |
| Product weight | 24 g |
| Type of mounting | Direct mounting via thread |
| Note on materials | RoHS-compliant |
| Material stops | High-alloy steel |
| Material seals | NBR |
| Material plate | Anodised wrought aluminium alloy |
| Material screws | Steel |