

# Displacement encoder MLO-POT-600-LWG

Part number: 152650

FESTO



 General operating condition

## Data sheet

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive
Functional principle of measuring system	Analogue
Ambient temperature	-30 °C ... 100 °C
Recommended wiper current	<1 µA
Max. wiper current, short-time	10000 µA
Max. travel speed	5 m/s
Max. travel acceleration	200 m/s <sup>2</sup>
Displacement resolution	0.01 mm
Non-dependent linearity	0.05 %
Temperature coefficient	5 ppm/K
Stroke	600 mm
Output signal	Analogue
Connection resistance	5 kOhm
Connection resistance tolerance	20 %
Nominal operating voltage DC	10 V
Max. operating voltage DC	42 V
Permissible voltage fluctuations	<1%
Max. current consumption	4 mA
Electrical connection	Plug Square design
Design	Round profile With operating rod
Angle offset of driver	±12.5°
Mounting position	Any
Product weight	1500 g
Material housing	anodised
Material cover	Reinforced PBT
Material connecting rod	High-alloy stainless steel
Material bearing seal	NBR
Material rod seal	PTFE
Degree of protection	IP65 To IEC 60529
Vibration resistance to DIN/IEC 68 Part 2-6	Tested to severity level 2
Continuous shock resistance to DIN/IEC 68 Part 2-82	Tested to severity level 2
LABS (PWIS) conformity	VDMA24364-B2-L