


Manifold sub-base VABX-A-S-BU-12-SHUH-U

Part number: 8191789

FESTO



 General operating condition

Data sheet

Feature	Value
Size	1 2
Grid dimension	19.05 mm
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Integrated function	With electrical interlinking module
Flow direction	Reversible
Compatible with	Valve terminal VTUX-A-S
Suitability for vacuum	Yes
Dimensions (W x L x H)	19.05 mm x 104.3 mm x 43.1 mm
Pollution degree	2
Approval	RCM
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 95%
Degree of protection	IP65
Overvoltage category	II
Ambient temperature	-5 °C ... 50 °C
Nominal altitude of use	< 3000 m NHN
Product weight	56.3 g
Electrical control	AP interface
Communication interface, protocol	AP
Mounting method for sub-base	With through-hole
Type of mounting	Tie rod
Pneumatic connection, port 1	For 15 mm cartridge
Pneumatic connection, port 5	For 15 mm cartridge
Note on materials	RoHS compliant
Material sub-base	Reinforced PA
Material seals	NBR
Material clip	High-alloy stainless steel