

Proportional-pressure regulator MPPE-3-1/2-10-010

Part number: 187326

FESTO



General operating condition

Data sheet

| Feature | Value |
|--|---|
| Nominal size, supply | 11 mm |
| Nominal size, exhaust | 12 mm |
| Type of actuation | Electric |
| Sealing principle | Soft |
| Mounting position | optional |
| Design | Piloted piston regulator |
| Short circuit current rating | For all electrical connections |
| Safety instructions | Safety position MPPE: if the power supply cable is interrupted, the output pressure drops to 0 bar. |
| Symbol | 00995304 |
| Reverse polarity protection | For all electrical connections |
| Valve function | 3-way proportional-pressure regulator, closed |
| Operating pressure | ≤1.2 MPa |
| Operating pressure | ≤12 bar |
| Pressure regulation range | 0 MPa ... 1 MPa |
| Pressure regulation range | 0 bar ... 10 bar |
| Inlet pressure 1 | 11 bar ... 12 bar |
| Inlet pressure 1 | 1.1 MPa ... 1.2 MPa |
| Max. pressure hysteresis | 0.005 MPa |
| Max. pressure hysteresis | 0.05 bar |
| Switching time off | 450 ms |
| Switching time on | 230 ms |
| Operational voltage range DC | 18 V ... 30 V |
| Nominal operating voltage DC | 24 V |
| Residual ripple | 10 % |
| SETPOINT/ACTUAL values | Voltage type 0 - 10 V |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Approval | RCM trademark |
| KC mark | KC-EMV |
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |

| Feature | Value |
|------------------------------|---|
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media temperature | 0 °C ... 60 °C |
| Degree of protection | IP65 |
| Ambient temperature | 0 °C ... 50 °C |
| Product weight | 2670 g |
| Electrical connection | M16x0.75 Plugs To DIN 45326 Round design |
| Type of mounting | With through-hole |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | G1/2 |
| Pneumatic connection, port 3 | G1/2 |
| Note on materials | RoHS-compliant |
| Material housing | Wrought aluminium alloy |
| Material membrane | NBR |