

Certificate of Compliance

Certificate Number **012208-MH19482**
Report Reference **MH19482-January 22, 2008**
Issue Date **2008 January 22**

Page 1 of 2



Issued to: **Festo Ag & Co Kg**
Ruiter Stra\DFe 82
Esslingen, 73734
Germany

This is to certify that representative samples of

Valving Systems



Cat. Nos. MS4-EE, MS4N-EE, MS6-EE or MS6N-EE, followed by 1/4, 1/8, 1/2, 3/8, AGA, AGB, AGC, AGD, AGE, AQK, AQN, AQP, AQR or AQS, followed by V24, 10V24 or V24P, may be followed by EX2, may be followed by S, may be followed by Z, followed by 527709, 527710, 527682 or 527683, followed by 4 suffixes consisting of any combination of letters and/or numbers.

Have been investigated by Underwriters Laboratories Inc.® in accordance with the Standard(s) indicated on this Certificate.

Standard(s) for Safety: **USR – Investigated to UL 429, Fifth Ed.**
CNR – Investigated to Canadian Standard C22.2, No. 139-1982, Second Ed.

Additional Information: **See Addendum**

Only those products bearing the UL Recognized Component Marks for the U.S. and Canada should be considered as being covered by UL's Recognition and Follow-Up Service and meeting the appropriate U.S. and Canadian requirements.

The UL Recognized Component Mark for the U.S. generally consists of the manufacturer's identification and catalog number, model number or other product designation as specified under "Marking" for the particular Recognition as published in the appropriate UL Directory. As a supplementary means of identifying products that have been produced under UL's Component Recognition Program, UL's Recognized Component Mark: , may be used in conjunction with the required Recognized Marks. The Recognized Component Mark is required when specified in the UL Directory preceding the recognitions or under "Markings" for the individual recognitions. The UL Recognized Component Mark for Canada consists of the UL Recognized Mark for Canada:  and the manufacturer's identification and catalog number, model number or other product designation as specified under "Marking" for the particular Recognition as published in the appropriate UL Directory.

Look for the UL Recognized Component Mark on the product

Issued by: Henry J. Wallerbos

Reviewed by: Richard J. Jokela

Henry J. Wallerbos, Project Handler

Richard J. Jokela, Reviewer

Underwriters Laboratories Inc.

Underwriters Laboratories Inc.

Any information and documentation involving UL Mark services are provided on behalf of Underwriters Laboratories Inc. (UL) or any authorized licensee of UL. For questions in The United States of America you may call 1-877-UL-HELPS.

Certificate of Compliance

Certificate Number **012208-MH19482**
Report Reference **MH19482-January 22, 2008**
Issue Date **2008 January 22**

Page 2 of 2



Fluid:	Air or inert gas
Maximum Operating Pressure Differential:	0.4-1.0 Mpa, 4-10 Bar, or 58-145 psi
Maximum External Body Pressure	0.4-1.0 Mpa, 4-10 Bar, or 58-145 psi
Maximum Fluid Temperature / ambient:	-10°C to +50°C
Electrical (for each separate pilot valve):	24 Vdc NEC Class 2 only, Max. 1.5 W

Issued by: Henry J. Wallerbos

Henry J. Wallerbos, Project Handler

Underwriters Laboratories Inc.

Reviewed by: Richard J. Jokela

Richard J. Jokela, Reviewer

Underwriters Laboratories Inc.

Any information and documentation involving UL Mark services are provided on behalf of Underwriters Laboratories Inc. (UL) or any authorized licensee of UL. For questions in The United States of America you may call 1-877-UL-HELPS.