

Compact cylinder ADVUL

FESTO



Type code

001	Series	
ADVUL	Compact cylinder, double-acting, secured against twisting by guide rod and yoke plate	

002	Piston diameter [mm]	
12	12	
16	16	
20	20	
25	25	
32	32	
40	40	
50	50	
63	63	
80	80	
100	100	

003	Stroke [mm]	
...	1 ... 400	

004	Cushioning	
P	Elastic cushioning rings/plates at both ends	

005	Position sensing	
A	For proximity sensor	

Datasheet

General technical data

Piston diameter	12 mm	16 mm	20 mm	25 mm	32 mm	40 mm	50 mm	63 mm	80 mm	100 mm
Structural design	Piston, Piston rod									
Pneumatic connection	M5				G1/8				G1/4	
Piston rod end	Internal thread									
Type of mounting	Alternatively:, With through-hole, With accessories									
Cushioning	Elastic cushioning rings/pads at both ends									
Position sensing	Via proximity switch									
Mounting position	Any									

Operating and environmental conditions – ADVUL-12 ... 40

Piston diameter	12 mm	16 mm	20 mm	25 mm	32 mm	40 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]					
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)					
Operating pressure	0.15 ... 1 MPa	0.12 ... 1 MPa	0.1 ... 1 MPa			
Operating pressure	1.2 ... 10 bar			1 ... 10 bar		
Operating pressure	21.75 ... 145 psi	17.4 ... 145 psi	14.5 ... 145 psi			
Ambient temperature ¹⁾	-20 ... 80°C					
Corrosion resistance class (CRC) ²⁾	2 - Moderate corrosion stress					

1) Note operating range of proximity switches.

2) For more information, visit www.festo.com/x/topic/kbk

Operating and environmental conditions – ADVUL-50 ... 100

Piston diameter	50 mm	63 mm	80 mm	100 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]			
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)			
Operating pressure	0.1 ... 1 MPa			
Operating pressure	1 ... 10 bar			
Operating pressure	14.5 ... 145 psi			
Ambient temperature ¹⁾	-20 ... 80°C			
Corrosion resistance class (CRC) ²⁾	2 - Moderate corrosion stress			

1) Note operating range of proximity switches.

2) For more information, visit www.festo.com/x/topic/kbk

Forces and impact energy

$$V = \sqrt{\frac{2 \cdot E}{m_1 + m_2}}$$

$$m_2 = \frac{2 \cdot E}{v^2} - m_1$$

V = permitted impact velocity

E = max. impact energy

m1 = moving mass (drive)

m2 = moving payload

Piston diameter	12 mm	16 mm	20 mm	25 mm	32 mm	40 mm	50 mm	63 mm	80 mm	100 mm
Theoretical force at 6 bar, advancing	68 N	121 N	188 N	295 N	483 N	754 N	1,178 N	1,870 N	3,016 N	4,712 N
Theoretical force at 6 bar, retracting	51 N	90 N	141 N	247 N	415 N	686 N	1,057 N	1,750 N	2,827 N	4,418 N
Impact energy in the end positions	0.07 J	0.1 J	0.14 J	0.1 J	0.4 J	0.52 J	0.64 J	0.7 J	0.75 J	1 J


Weights

Piston diameter	12 mm	16 mm	20 mm	25 mm	32 mm	40 mm	50 mm	63 mm	80 mm	100 mm
Basic weight with 0 mm stroke	100 g	103 g	179 g	215 g	362 g	517 g	707 g	1,252 g	2,150 g	3,316 g
Additional weight per 10 mm stroke	14 g	16 g	26 g	28 g	38 g	45 g	64 g	72 g	97 g	116 g


Datasheet

Materials										
Piston diameter	12 mm	16 mm	20 mm	25 mm	32 mm	40 mm	50 mm	63 mm	80 mm	100 mm
Material of cylinder barrel	Wrought aluminum alloy									
Cover material	Wrought aluminum alloy									
Piston rod material	high-alloy stainless steel						High-alloy steel			
Flange screws material	high-alloy stainless steel		Steel, galvanized							
Material of dynamic seals	NBR, TPE-U(PU)									

Max. lateral force Fq as a function of projection x




Torque M as a function of stroke l



Dimensions

Dimensions – Basic cylinder

Download CAD data www.festo.com

[1] Minimum screw-in depth

[2] + = plus stroke length


	BG ¹⁾	D1 ø H9	D5	D6	D7 ø H9	E	EE	FB ø H8	H	L2
ADVUL-12	18,5	6	14	M3	–	29	M5	3	1	38
ADVUL-16	18,5	6	14	M3	–	29	M5	3	1	38
ADVUL-20	18,5	6	17	M4	–	36	M5	4	1,5	38
ADVUL-25	18,5	6	22	M5	14	40	M5	5	1,5	39,5
ADVUL-32	21,5	6	28	M5	17	50	G1/8	5	2	44,5
ADVUL-40	21,5	6	33	M5	17	60	G1/8	5	2,5	45,5
ADVUL-50	22	6	42	M6	22	68	G1/8	6	3	45,5
ADVUL-63	24,5	8	50	M6	22	87	G1/8	6	4	50
ADVUL-80	27,5	8	65	M8	28	107	G1/8	8	4	56
ADVUL-100	32,5	8	80	M10	30	128	G1/4	10	5	66,5

	L3	L4	ME	MM ø	PL	RT	T1 +0,2	T2 –0,2	TG	⌀1 h13
ADVUL-12	3	16	6	6	8	M4	–	4	18	5
ADVUL-16	3	16	6	8	8	M4	–	4	18	7
ADVUL-20	4	18	8	10	8	M5	–	4	22	9
ADVUL-25	4	18	8	10	8	M5	4,8	4	26	9
ADVUL-32	5	20	10	12	8	M6	6,1	4	32	10
ADVUL-40	5	20	10	12	8	M6	6,1	4	42	10
ADVUL-50	6	20	12	16	8	M8	7,6	4	50	13
ADVUL-63	8	25	12	16	8	M10	7,6	4	62	13
ADVUL-80	8	25	14	20	8,5	M10	8,7	4	82	17
ADVUL-100	8	25	14	25	10,5	M10	10,3	4	103	22

1) Do not exceed the screw-in depth

Dimensions

Dimensions – Piston rod at one end Download CAD data www.festo.com




[1] += plus stroke length

	WH	ZJ
ADVUL-12	4,5	42,5
ADVUL-16	4,5	42,5
ADVUL-20	4,5	42,5
ADVUL-25	5,5	45
ADVUL-32	6	50,5
ADVUL-40	6,5	52
ADVUL-50	7,5	53
ADVUL-63	7,5	57,5
ADVUL-80	8	64
ADVUL-100	10	76,5

Dimensions


Dimensions – Flange mounting FUA

Download CAD data www.festo.com

[1] += plus stroke length

	E	FB ø	MF	R	TF	UF	ZF
FUA-12/16	29	5,5	10	–	43	55	52,5
FUA-20	36	6,6	10	–	55	70	52,5
FUA-25	40	6,6	10	–	60	76	55
FUA-32	50	7	10	32	65	80	60,5
FUA-40	60	9	10	36	82	102	62
FUA-50	68	9	12	45	90	110	65
FUA-63	87	9	15	50	110	130	72,5
FUA-80	107	12	15	63	135	160	76
FUA-100	128	14	15	75	163	190	91,5

Dimensions




	CD Ø	EW	FL	L	MR	XC
SUA-12/16	6	12	16	10	6	58,5
SUA-20	8	16	20	14	8	62,5
SUA-25	8	16	20	14	8	64

Dimensions

Dimensions – Swivel flange SUA for ADVUL-32 ... 100

Download CAD data www.festo.com




[1] += plus stroke length

	CB	CD ø	FL	L	ML	MR	UB	XC
SUA-32	26	10	22	13	54	10	45	72,5
SUA-40	28	12	25	16	62	12	52	77
SUA-50	32	12	27	16	70	12	60	80
SUA-63	40	16	32	21	82	16	70	89,5
SUA-80	50	16	36	23	102	16	90	100
SUA-100	60	20	41	26	126	20	110	117,5

Dimensions

Dimensions – Mounting kit DPVU Download CAD data www.festo.com



[1] The maximum total stroke length may not be exceeded when combining cylinders and multi-position kits.

	B1	H	1)
DPVU-12/16	12,5	38	400
DPVU-20	12,5	38	
DPVU-25	13	39,5	
DPVU-32	14,5	44,5	600
DPVU-40	14,5	45,5	
DPVU-50	14,5	45,5	
DPVU-63	14,5	50	
DPVU-80	16,5	56	800
DPVU-100	19,5	66,5	

1) Max. total stroke length [mm]

Ordering data


ADVUL			
Piston diameter	Stroke	Part no.	Type
12 mm	1 ... 200 mm	156200	ADVUL-12- -P-A
	5 mm	156844	ADVUL-12-5-P-A
	10 mm	156845	ADVUL-12-10-P-A
	15 mm	156846	ADVUL-12-15-P-A
	20 mm	156847	ADVUL-12-20-P-A
	25 mm	156848	ADVUL-12-25-P-A
	30 mm	156849	ADVUL-12-30-P-A
	40 mm	156850	ADVUL-12-40-P-A
16 mm	1 ... 200 mm	156201	ADVUL-16- -P-A
	5 mm	156851	ADVUL-16-5-P-A
	10 mm	156852	ADVUL-16-10-P-A
	15 mm	156853	ADVUL-16-15-P-A
	20 mm	156854	ADVUL-16-20-P-A
	25 mm	156855	ADVUL-16-25-P-A
	30 mm	156856	ADVUL-16-30-P-A
	40 mm	156857	ADVUL-16-40-P-A
20 mm	1 ... 200 mm	156202	ADVUL-20- -P-A
	5 mm	156858	ADVUL-20-5-P-A
	10 mm	156859	ADVUL-20-10-P-A
	15 mm	156860	ADVUL-20-15-P-A
	20 mm	156861	ADVUL-20-20-P-A
	25 mm	156862	ADVUL-20-25-P-A
	30 mm	156863	ADVUL-20-30-P-A
	40 mm	156864	ADVUL-20-40-P-A
25 mm	1 ... 200 mm	156203	ADVUL-25- -P-A
	5 mm	156866	ADVUL-25-5-P-A
	10 mm	156867	ADVUL-25-10-P-A
	15 mm	156868	ADVUL-25-15-P-A
	20 mm	156869	ADVUL-25-20-P-A
	25 mm	156870	ADVUL-25-25-P-A
	30 mm	156871	ADVUL-25-30-P-A
	40 mm	156872	ADVUL-25-40-P-A
32 mm	1 ... 300 mm	156204	ADVUL-32- -P-A
	5 mm	156874	ADVUL-32-5-P-A
	10 mm	156875	ADVUL-32-10-P-A
	15 mm	156876	ADVUL-32-15-P-A
	20 mm	156877	ADVUL-32-20-P-A
	25 mm	156878	ADVUL-32-25-P-A
	30 mm	156879	ADVUL-32-30-P-A
	40 mm	156880	ADVUL-32-40-P-A
40 mm	1 ... 300 mm	156205	ADVUL-40- -P-A
	5 mm	156884	ADVUL-40-5-P-A
	10 mm	156885	ADVUL-40-10-P-A
	15 mm	156886	ADVUL-40-15-P-A
	20 mm	156887	ADVUL-40-20-P-A
	25 mm	156888	ADVUL-40-25-P-A
	30 mm	156889	ADVUL-40-30-P-A
	40 mm	156890	ADVUL-40-40-P-A
50 mm	1 ... 300 mm	156206	ADVUL-50- -P-A
	10 mm	156894	ADVUL-50-10-P-A
	15 mm	156895	ADVUL-50-15-P-A
	20 mm	156896	ADVUL-50-20-P-A
	25 mm	156897	ADVUL-50-25-P-A

Ordering data

ADVUL			
Piston diameter	Stroke	Part no.	Type
50 mm	30 mm	156898	ADVUL-50-30-P-A
	40 mm	156899	ADVUL-50-40-P-A
	50 mm	156900	ADVUL-50-50-P-A
	60 mm	156901	ADVUL-50-60-P-A
	80 mm	156902	ADVUL-50-80-P-A
63 mm	1 ... 300 mm	156207	ADVUL-63- -P-A
	10 mm	156903	ADVUL-63-10-P-A
	15 mm	156904	ADVUL-63-15-P-A
	20 mm	156905	ADVUL-63-20-P-A
	25 mm	156906	ADVUL-63-25-P-A
	30 mm	156907	ADVUL-63-30-P-A
	40 mm	156908	ADVUL-63-40-P-A
	50 mm	156909	ADVUL-63-50-P-A
	60 mm	156910	ADVUL-63-60-P-A
	80 mm	156911	ADVUL-63-80-P-A
80 mm	1 ... 400 mm	156208	ADVUL-80- -P-A
	10 mm	156912	ADVUL-80-10-P-A
	15 mm	156913	ADVUL-80-15-P-A
	20 mm	156914	ADVUL-80-20-P-A
	25 mm	156915	ADVUL-80-25-P-A
	30 mm	156916	ADVUL-80-30-P-A
	40 mm	156917	ADVUL-80-40-P-A
	50 mm	156918	ADVUL-80-50-P-A
	60 mm	156919	ADVUL-80-60-P-A
	80 mm	156920	ADVUL-80-80-P-A
100 mm	1 ... 400 mm	156209	ADVUL-100- -P-A
	10 mm	156921	ADVUL-100-10-P-A
	15 mm	156922	ADVUL-100-15-P-A
	20 mm	156923	ADVUL-100-20-P-A
	25 mm	156924	ADVUL-100-25-P-A
	30 mm	156925	ADVUL-100-30-P-A
	40 mm	156926	ADVUL-100-40-P-A
	50 mm	156927	ADVUL-100-50-P-A
	60 mm	156928	ADVUL-100-60-P-A
	80 mm	156929	ADVUL-100-80-P-A

Peripherals overview

Peripherals overview




Accessories		→ Page/Internet
Type/order code	Description	
[1] Compact cylinder ADVUL	Pneumatic drive	advul
[2] One-way flow control valve GRLA	For speed control	grla

Peripherals overview


Accessories		→ Page/Internet
Type/order code	Description	
[3] Push-in fitting QS	For connecting compressed air tubing with standard O.D.	qs
[4] Flange mounting FUA	For end cap	15
[5] Swivel flange SUA for diameter 12 ... 25	For end cap	15
[6] Clevis foot LBN	–	16
[7] Swivel flange SUA for diameter 32 ... 100	For end cap	15
[8] Mounting kit DPVU	For connecting two cylinders with the same piston diameter to form a multi-position cylinder	15
[9] Clevis foot LN	–	16
[10] Clevis foot LNG	–	16
[11] Clevis foot LSN	With spherical bearing	16
[12] SNCL swivel flange	–	15
[13] Proximity switch SME-8	Can be integrated in the cylinder profile barrel	17
[13] Proximity switch SMT-8	Can be integrated in the cylinder profile barrel	16
[14] Slot cover ABP-5-S	To protect the sensor cables and the sensor slots from contamination	18

Accessories


Flange mounting FUA

	Description	Mounting material	Product weight	Part no.	Type
	for diameter 12/16	Wrought aluminum alloy	48 g	157299	FUA-12/16
	For diameter 20		77 g	157300	FUA-20
	For diameter 25		91 g	157301	FUA-25
	for Ø 32		290 g	157302	FUA-32
	for Ø 40		449 g	157303	FUA-40
	for Ø 50		658 g	157304	FUA-50
	for Ø 63		1,277 g	157305	FUA-63
	for Ø 80		1,910 g	157306	FUA-80
	for Ø 100		2,716 g	157307	FUA-100


Swivel flange SUA

	Description	Mounting material	Product weight	Part no.	Type
	for diameter 12/16	Wrought aluminum alloy	22 g	157319	SUA-12/16
	For diameter 20		41 g	157320	SUA-20
	For diameter 25		45 g	157321	SUA-25
	for Ø 32		138 g	157322	SUA-32
	for Ø 40		199 g	157323	SUA-40
	for Ø 50		288 g	157324	SUA-50
	for Ø 63		531 g	157325	SUA-63
	for Ø 80		764 g	157326	SUA-80
	for Ø 100		1,285 g	157327	SUA-100


SNCL swivel flange

	Description	Mounting material	Product weight	Part no.	Type
	for Ø 32	Die-cast aluminum	71 g	174404	SNCL-32
	for Ø 40		95 g	174405	SNCL-40
	for Ø 50		158 g	174406	SNCL-50
	for Ø 63		225 g	174407	SNCL-63
	for Ø 80		436 g	174408	SNCL-80
	for Ø 100		606 g	174409	SNCL-100

Mounting kit DPVU

	Description	Material of flange	Product weight	Part no.	Type
	for diameter 12/16	Wrought aluminum alloy	35 g	161194	DPVU-12/16
	For diameter 20		54 g	161195	DPVU-20
	For diameter 25		65 g	161196	DPVU-25
	for Ø 32		111 g	161197	DPVU-32
	for Ø 40		155 g	161198	DPVU-40
	for Ø 50		212 g	161199	DPVU-50
	for Ø 63		372 g	161200	DPVU-63
	for Ø 80		580 g	161201	DPVU-80
	for Ø 100		935 g	161202	DPVU-100

Connecting two cylinders with the same piston diameter to form a three- or four-position cylinder




A multi-position cylinder consists of two separate cylinders whose piston rods extend in opposite directions. This means that depending on actuation and stroke configuration, this type of cylinder can assume up to four positions. In each case the cylinder is driven precisely against a stop.


Note that when one end of the piston rod is fixed, the cylinder barrel executes the movement. This means that the connections to the cylinder have to be flexible.


Achieving 3 positions: two cylinders of the same stroke length have to be connected together


Achieving 4 positions: two cylinders with different stroke lengths have to be connected together


Accessories

Clevis foot LBN					
	Description	Mounting material	Product weight	Part no.	Type
	for diameter 12/16	Steel, Galvanized	40 g	6058	LBN-12/16
	for diameter 20/25		84 g	6059	LBN-20/25

Clevis foot LN					
	Description	Mounting material	Product weight	Part no.	Type
	for Ø 32	Quenched and tempered steel	149 g	5147	LN-32
	for Ø 40		192 g	5148	LN-40
	for Ø 50		322 g	5149	LN-50
	for Ø 63	Spheroidal graphite cast iron	492 g	5150	LN-63
	for Ø 80		793 g	5151	LN-80
	for Ø 100		1,232 g	5152	LN-100

Clevis foot LNG					
	Description	Mounting material	Product weight	Part no.	Type
	for Ø 32	Quenched and tempered steel	133 g	33890	LNG-32
	for Ø 40		161 g	33891	LNG-40
	for Ø 50		281 g	33892	LNG-50
	for Ø 63	Spheroidal graphite cast iron	439 g	33893	LNG-63
	for Ø 80		727 g	33894	LNG-80
	for Ø 100		1,139 g	33895	LNG-100


Clevis foot LSN					
	Description	Mounting material	Product weight	Part no.	Type
	for Ø 32	High-alloy steel	162 g	5561	LSN-32
	for Ø 40		219 g	5562	LSN-40
	for Ø 50		366 g	5563	LSN-50
	for Ø 63	Spheroidal graphite cast iron	472 g	5564	LSN-63
	for Ø 80		755 g	5565	LSN-80
	for Ø 100		1,166 g	5566	LSN-100

SMT proximity switch for T-slot, magneto-resistive						Link smt
	Type of mounting	Switching output	Electrical connection	Cable length	Part no.	Type
	Screwed on, Can be inserted in slot from above	3-wire NPN N/O contact	Open end	2.5 m	574338	SMT-8M-A-NS-24V-E-2,5-OE
			Plug M8, A-coded	0.3 m	574339	SMT-8M-A-NS-24V-E-0,3-M8D
		3-wire PNP N/C contact	Open end	7.5 m	574340	SMT-8M-A-PO-24V-E-7,5-OE
				2.5 m	574335	SMT-8M-A-PS-24V-E-2,5-OE
		3-wire PNP N/O contact	Plug M8, A-coded	0.3 m	574334	SMT-8M-A-PS-24V-E-0,3-M8D
			Plug M12, A-coded		574337	SMT-8M-A-PS-24V-E-0,3-M12


Accessories

Proximity switch SME for T-slot, magnetic, reed


Link [sme](#)

	Type of mounting	Switching output	Electrical connection	Cable length	Part no.	Type
	Screwed on, Can be inserted in slot from above	3-wire N/C contact	Open end	7.5 m	546799	SME-8M-DO-24V-K-7,5-OE
		3-wire N/O contact		2.5 m	543862	SME-8M-DS-24V-K-2,5-OE
				5 m	543863	SME-8M-DS-24V-K-5,0-OE
		Plug M8, A-coded	0.3 m	543861	SME-8M-DS-24V-K-0,3-M8D	
		2-wire N/O contact	Open end	2.5 m	543872	SME-8M-ZS-24V-K-2,5-OE


Connecting cables NEBA, straight, M8 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/wires	Cable length	Part no.	Type
	M8x1 A-coded as per EN 61076-2-104	Open end	3	2.5 m	8078223	NEBA-M8G3-U-2.5-N-LE3
				5 m	8078224	NEBA-M8G3-U-5-N-LE3


Connecting cables NEBA, straight, M12 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/wires	Cable length	Part no.	Type
	M12x1 A-coded as per EN 61076-2-101	Open end	3	2.5 m	8078236	NEBA-M12G5-U-2.5-N-LE3
				5 m	8078237	NEBA-M12G5-U-5-N-LE3


Connecting cables NEBA, angled, M8 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/wires	Cable length	Part no.	Type
	M8x1 A-coded as per EN 61076-2-104	Open end	3	2.5 m	8078230	NEBA-M8W3-U-2.5-N-LE3
				5 m	8078231	NEBA-M8W3-U-5-N-LE3

Connecting cables NEBA, angled, M12 connection

	Electrical connection 1, connection technology	Electrical connection 2, connection technology	Electrical connection 2, number of pins/wires	Cable length	Part no.	Type
	M12x1 A-coded as per EN 61076-2-101	Open end	3	2.5 m	8078245	NEBA-M12W5-U-2.5-N-LE3
				5 m	8078246	NEBA-M12W5-U-5-N-LE3

Accessories

Slot cover ABP for T-slot				
	Description	Packaging quantity [pieces]	Part no.	Type
	Length 0.5 m, Insertable	2	151680	ABP-5-S