

Suction cup with connection VAS, VASB

FESTO



Characteristics

At a glance

- Sturdy and reliable
- Suction cups with fixed connecting thread
- 3 materials
- 11 diameters of suction cup with connector available
- 2 suction cup shapes: round (VAS), protective bellows (VASB)
- Vacuum port on top, on the side
- Screw-in thread

Engineering tools Link [smart-vacuum](#)



Save time with engineering tools: Smart engineering for the optimal solution. Our goal is to increase your productivity. Our engineering tools play an integral part in achieving this goal. They help you size your system correctly, tap into unimagined productivity reserves and generate additional productivity along the entire value chain. In every phase of your project, from the initial contact to the modernisation of your machine, you will come across a number of different tools that will be of use to you.

The vacuum engineering tool provides you with a product recommendation based on your vacuum application requirements. After entering a number of parameters, the vacuum calculator recommends the Festo products required for an optimum solution.

Diagrams Link [vas](#)



The diagrams shown in this document are also available online. These can be used to display precise values.

Material

[PUR]	Polyurethane	[NBR]	Nitrile rubber
• Long service life • Gentle treatment thanks to soft material		• For universal use • Also available for battery production (F1A) in suction cup sizes 8 to 55	
[SI]	Silicone		
• High temperature resistance • Suitable for use in the food industry			

Special material properties

[F1A]	Recommended for production plants for manufacturing lithium-ion batteries, F1A
-------	--

Application note: Foreign particles can adhere to the product or form during installation. Depending on the application, it may be necessary to purge the product with clean compressed air, to clean it after installation and to operate it with ducted exhaust air.

Characteristics

Application example



A large application area for vacuum technology is flexible automation:

- Lifting
- Equipping
- Moving
- Inserting
- Conveying
- Gripping
- Holding
- Stacking
- Clamping
- Transporting
- Repositioning
- Turning

Type code

001	Series	
VAS	Suction cup complete	
VASB	Suction cups with connection, protective bellows	

002	Suction cup size	
2	2 mm diameter	
5	5 mm diameter	
8	8 mm diameter	
10	10 mm diameter	
15	15 mm diameter	
30	30 mm diameter	
40	40 mm diameter	
55	55 mm diameter	
75	75 mm diameter	
100	100 mm diameter	
125	125 mm diameter	

003	Vacuum port	
G14	G1/4	
G18	G1/8	
G38	G3/8	
M3	M3	
M5	M5	

004	Connection position	
	Top	
S	On the side	

005	Material	
PUR	Polyurethane	
NBR	Nitrile rubber	
SI	Silicone	

006	Special material properties	
	None	
F1A	Recommended for production plants for manufacturing lithium-ion batteries, F1A	

007	Generation	
	Standard	
B	B-series	

Datasheet

Technical data – Suction cup with connection VAS-...-S-PUR-B, vacuum connection on the side

Suction cup diameter	8 mm
Vacuum connection	M5
Position of connection	On the side
Nominal size	2 mm
Suction cup shape	Round, flat
Type of mounting	Via vacuum port
Mounting position	Any
Nominal operating pressure	-0.7 bar
Holding force at nominal operating pressure	2.8 N
Effective suction diameter	7.1 mm
Suction cup volume	0.095 cm ³
Height compensator for suction cup	0.9 mm
Operating pressure	-0.95 ... 0 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Ambient temperature	-20 ... 60°C
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress
Shore hardness	60 +/-5
Material suction cup	TPE-U(PU)
Material screwed plug	Brass
Note on materials	RoHS compliant

1) More information: www.festo.com/x/topic/crc**Technical data – Suction cup with connection VAS-...-NBR**


Suction cup diameter	2 mm	5 mm	10 mm	75 mm	100 mm	125 mm
Vacuum connection	M3	M5		G1/4		G3/8
Position of connection	On top					
Nominal size	1 mm	1.5 mm	2 mm	4 mm		7 mm
Suction cup shape	Round, flat					
Type of mounting	Via vacuum port					
Mounting position	Any					
Nominal operating pressure	-0.7 bar					
Holding force at nominal operating pressure	0.14 N	0.9 N	4.5 N	197 N	397 N	606 N
Effective suction diameter	1.6 mm	4 mm	9 mm	60 mm	85 mm	105 mm
Suction cup volume	0.03 cm³		0.12 cm³	8.01 cm³	33.5 cm³	79.1 cm³
Height compensator for suction cup	0.5 mm		1.1 mm	3.5 mm		6 mm
Operating pressure	-0.95 ... 0 bar					
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]					
Ambient temperature	-20 ... 80°C					
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress					
Shore hardness	55 +/-5		60 +/-5	70 +/- 5		
Material suction cup	NBR					
Material screwed plug	High-alloy steel	Wrought aluminium alloy		Die-cast zinc		
Note on materials	RoHS compliant					

1) More information: www.festo.com/x/topic/crc**Additional features – suction cup with connection VAS-...-NBR-F1A (for battery production)**


Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Material suction cup	NBR
Material screwed plug	Wrought aluminium alloy
LABS (PWIS) conformity	VDMA24364-A1/A2-L

Datasheet

Theoretical suction force F as a function of vacuum pu - VAS-1 ... 15




Theoretical suction force F as a function of vacuum pu - VAS-30 ... 125




Datasheet


Suction cup volume – VAS-8



Suction cup volume – VAS-15 ... 100



Suction cup volume – VAS-125



Datasheet

General technical data – Suction cup with connection VAS-...-SI-B/PUR-B

Suction cup diameter	8 mm	10 mm	15 mm	30 mm	40 mm	55 mm	75 mm	100 mm	125 mm
Vacuum connection	M5		G1/8		G1/4				G3/8
Position of connection	On top								
Nominal size	2 mm		3 mm		4 mm				7 mm
Suction cup shape	Round, flat								
Type of mounting	Via vacuum port								
Mounting position	Any								
Nominal operating pressure	-0.7 bar								
Holding force at nominal operating pressure	2.6 ... 2.8 N	3.7 ... 4 N	8.5 N	31 ... 34 N	58 ... 60 N	110 N	245 ... 250 N	450 ... 464 N	570 ... 700 N
Suction cup volume	0.095 cm ³	0.12 cm ³	0.228 ... 0.328 cm ³	1.29 cm ³	3.47 cm ³	8.01 cm ³	18.3 cm ³	33.5 cm ³	79.1 cm ³
Height compensator for suction cup	0.9 mm	1.1 mm	1.2 mm	1.9 mm	3 mm	3.5 mm			6 mm
Operating pressure	-0.95 ... 0 bar								
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]								
Ambient temperature	-40 ... 200°C								
Suitable for use with food	See supplementary material information								
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress								
Shore hardness	60 +/-5								
Material suction cup	PUR, VMQ (silicone)								
Material screwed plug	Wrought aluminium alloy, Brass				Wrought aluminium alloy, Die-cast zinc				
Note on materials	RoHS compliant								

1) More information: www.festo.com/x/topic/crc

Technical data – Suction cup with connection VASB-...-NBR, protective bellows


Suction cup diameter	75 mm	100 mm	125 mm
Vacuum connection	G1/4		G3/8
Position of connection	On top		
Nominal size	4 mm		7 mm
Suction cup shape	Round protective bellows 1.5-fold		
Type of mounting	Via vacuum port	–	Via vacuum port
Mounting position	Any	–	Any
Nominal operating pressure	-0.7 bar	–	-0.7 bar
Holding force at nominal operating pressure	197 N	397 N	606 N
Effective suction diameter	60 mm	85 mm	105 mm
Suction cup volume	65.5 cm ³	–	307 cm ³
Height compensator for suction cup	15.5 mm	–	25 mm
Operating pressure	-0.95 ... 0 bar	–	-0.95 ... 0 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]		
Ambient temperature	-20 ... 80°C		
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress	–	2 - Moderate corrosion stress
Shore hardness	60 +/-5		
Material suction cup	NBR		
Material screwed plug	Die-cast zinc		
Note on materials	RoHS compliant		

1) More information: www.festo.com/x/topic/crc


Additional features – suction cup with connection VAS-...-NBR-F1A (for battery production)

Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Material suction cup	NBR
Material screwed plug	Wrought aluminium alloy
LABS (PWIS) conformity	VDMA24364-A1/A2-L

Datasheet


Theoretical suction force F as a function of vacuum p_u – VASB-30 ... 125

Suction cup volume – VASB-8




Datasheet

Suction cup volume – VASB-15 ... 100



Suction cup volume – VASB-125



Datasheet

Technical data – Suction cup with connection VASB-...-SI-B, protective bellows

Suction cup diameter	8 mm	15 mm	30 mm	40 mm	55 mm	75 mm	100 mm	125 mm
Vacuum connection	M5	G1/8		G1/4				G3/8
Position of connection	On top							
Nominal size	2 mm	3 mm		4 mm				7 mm
Suction cup shape	Round protective bellows 1.5-fold							
Type of mounting	Via vacuum port							
Mounting position	Any							
Nominal operating pressure	-0.7 bar							
Holding force at nominal operating pressure	2.6 N	8.5 N	25 N	58 N	110 N	228 N	395 N	610 N
Suction cup volume	0.163 cm ³	0.83 cm ³	6.18 cm ³	11.11 cm ³	30.4 cm ³	65.5 cm ³	128 cm ³	307 cm ³
Height compensator for suction cup	3.3 mm	5.6 mm	13.9 mm	13.7 mm	20 mm	15.5 mm		25 mm
Operating pressure	-0.95 ... 0 bar							
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]							
Ambient temperature	-40 ... 200°C							
Suitable for use with food	See supplementary material information							
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress							
Shore hardness	60 +/-5							
Material suction cup	VMQ (silicone)							
Material screwed plug	Wrought aluminium alloy							
Note on materials	RoHS compliant							

1) More information: www.festo.com/x/topic/crc**Technical data – Suction cup with connection VASB-...-PUR-B, protective bellows**


Technical data - Suction cup with connection VASB III FOR B, protective bellows								
Suction cup diameter	8 mm	15 mm	30 mm	40 mm	55 mm	75 mm	100 mm	125 mm
Vacuum connection	M5	G1/8	G1/4					G3/8
Position of connection	On top							
Nominal size	2 mm	3 mm	4 mm					7 mm
Suction cup shape	Round protective bellows 1.5-fold							
Type of mounting	Via vacuum port							
Mounting position	Any							
Nominal operating pressure	-0.7 bar							
Holding force at nominal operating pressure	2.8 N	8.5 N	34 N	60 N	110 N	250 N	450 N	570 N
Suction cup volume	0.163 cm³	0.83 cm³	6.18 cm³	11.11 cm³	30.4 cm³	65.5 cm³	128 cm³	307 cm³
Height compensator for suction cup	3.3 mm	5.6 mm	13.9 mm	13.7 mm	20 mm	15.5 mm	25 mm	
Operating pressure	-0.95 ... 0 bar							
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]							
Ambient temperature	-20 ... 60°C							
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress							
Shore hardness	60 +/-5							
Material suction cup	PUR							
Material screwed plug	Brass			Die-cast zinc				
Note on materials	RoHS compliant							

1) More information: www.festo.com/x/topic/crc

Dimensions

Dimensions – Dimensions – Suction cup with connector VAS-...-S-PUR-B, vacuum connection on the side


Download CAD data www.festo.com



	B1	D	D2 Ø	D3 Ø	D4 Ø	L	L1	L2 -0,1	☐
VAS-8-...-S-PUR-B	13,5	M5	8	2	3,6	19	11,5	5	8

Dimensions

Dimensions – Dimensions – Suction cup with connector VAS-...-NBR

[Download CAD data](#) www.festo.com



[2] VAS-5/10: sealing ring OK; VAS-8/15 ... 125: sealing ring OL

	D	D1 Ø	D2 Ø	L	L1	L2	L3	≈G
VAS-2-...-NBR ¹⁾	M3	1	2	9,4	5,4	3,3	6,1	4,5
VAS-5-...-NBR	M5	2	5	16,5	10	3,8	12,7	8
VAS-8-...-NBR	M5	2	8	19,2	11,5	2,8	16,2	8
VAS-10-...-NBR	M5	2	10	19,2	11,5	3,8	15,4	8
VAS-15-...-NBR	G1/8	3	15	20,2	12	4,8	15,4	13
VAS-30-...-NBR	G1/8	3	30	21,5	12	4,8	16,7	13
VAS-40-...-NBR	G1/4	4	40	30,5	17	5,8	24,7	17
VAS-55-...-NBR	G1/4	4	55	32,5	17	5,8	26,7	17
VAS-75-...-NBR	G1/4	4	75	28	17	5,8	22,2	17
VAS-100-...-NBR	G1/4	4	100	28	17	5,8	22,2	17
VAS-125-...-NBR	G3/8	7	125	36	20	6,05	29,95	19
VAS-8-...-NBR-F1A	M5	2	8	19,2	11,5	2,8	16,4	8
VAS-15-...-NBR-F1A	G1/8	3	15	20,2	12	4,8	15,4	13
VAS-30-...-NBR-F1A	G1/8	3	30	21,5	12	4,8	16,7	13
VAS-40-...-NBR-F1A	G1/4	4	40	30,5	17	5,8	24,7	17
VAS-55-...-NBR-F1A	G1/4	4	55	32,5	17	5,8	26,7	17

1) Sealing ring is not included in the scope of delivery.

Dimensions

Dimensions – Dimensions – Suction cup VAS-...-SI-B [Download CAD data](#) www.festo.com




	D	D1 ø	D2 ø	L	L1	L4	⌀
VAS-8-...-SI-B	M5	2	8	19,2	11,5	4,3	8
VAS-10-...-SI-B	M5	2	10	19,2	11,5	4,3	8
VAS-15-...-SI-B	G1/8	3	15	20	12	6,5	13
VAS-30-...-SI-B	G1/8	3	30	21,5	12	6,5	13
VAS-40-...-SI-B	G1/4	4	40	30,5	17	8	17
VAS-55-...-SI-B	G1/4	4	55	33,5	17	8	17
VAS-75-...-SI-B	G1/4	4	75	28,2	17	8	17
VAS-100-...-SI-B	G1/4	4	100	28	17	8	17
VAS-125-...-SI-B	G3/8	7	125	36	20	12	19

Dimensions

Dimensions – Dimensions – Suction cup with connector VAS-...-PUR-B

Download CAD data www.festo.com




[1] Sealing ring

	D	D1 Ø	D2 Ø	L	L1	L2	L3	≙
VAS-8-...-PUR-B	M5	2	8	19	11,3	2,85	16,15	8
VAS-10-...-PUR-B	M5	2	10	19,2	11,5	2,85	16,35	8
VAS-15-...-PUR-B	G1/8	3	15	20	12	4,7	15,3	13
VAS-30-...-PUR-B	G1/8	3	30	21,5	12	4,7	16,8	13
VAS-40-...-PUR-B	G1/4	4	40	29,5	17	5,8	23,7	17
VAS-55-...-PUR-B	G1/4	4	55	32,5	17	5,8	26,7	17
VAS-75-...-PUR-B	G1/4	4	75	28	17	5,8	22,2	17
VAS-100-...-PUR-B	G1/4	4	100	28	17	5,8	22,2	17
VAS-125-...-PUR-B	G3/8	7	125	36	20	6,45	29,55	19

Dimensions

Dimensions – Dimensions – Suction cup with connector VASB-...-NBR, protective bellows

Download CAD data www.festo.com




[1] Sealing ring OL

	D	D1 Ø	D2 Ø	L	L1	L2	L3	≙
VASB-8-...-NBR	M5	2	8	22,7	11,5	2,8	19,9	8
VASB-15-...-NBR	G1/8	3	15	25	12	4,8	20,2	13
VASB-30-...-NBR	G1/8	3	30	34	12	4,8	29,2	13
VASB-40-...-NBR	G1/4	4	40	43	17	5,8	37,2	17
VASB-55-...-NBR	G1/4	4	55	52	17	5,8	46,2	17
VASB-75-...-NBR	G1/4	4	75	43,5	17	5,8	37,7	17
VASB-100-...-NBR	G1/4	4	100	44	17	5,8	38,2	17
VASB-125-...-NBR	G3/8	7	125	60	20	6	54	19
VASB-8-...-NBR-F1A	M5	2	8	22,7	11,5	2,8	19,9	8
VASB-15-...-NBR-F1A	G1/8	3	15	25	12	4,8	20,2	13
VASB-30-...-NBR-F1A	G1/8	3	30	34	12	4,8	29,2	13
VASB-40-...-NBR-F1A	G1/4	4	40	43	17	5,8	37,2	17
VASB-55-...-NBR-F1A	G1/4	4	55	52	17	5,8	46,2	17

Dimensions

Dimensions – Dimensions – Suction cup VASB-...-SI-B, protective bellows


Download CAD data www.festo.com



	D	D1 Ø	D2 Ø	L	L1	L4	≅
VASB-8-...-SI-B	M5	2	8	22,5	11,5	4,3	8
VASB-15-...-SI-B	G1/8	3	15	25,5	12	6,5	13
VASB-30-...-SI-B	G1/8	3	30	34	12	6,5	13
VASB-40-...-SI-B	G1/4	4	40	43	17	8	17
VASB-55-...-SI-B	G1/4	4	55	52	17	8	17
VASB-75-...-SI-B	G1/4	4	75	43,7	14,2	8	17
VASB-100-...-SI-B	G1/4	4	100	43,7	14,2	8	17
VASB-125-...-SI-B	G3/8	7	125	60	16,4	9	19

Dimensions

Dimensions – Dimensions – Vacuum cup VASB-...PUR-B, bellows Download CAD data www.festo.com



	D	D1 Ø	D2 Ø	L	L1	L2	L3	≈
VASB-8-...-PUR-B	M5	2	8	22,5	11,5	3,55	18,95	8
VASB-15-...-PUR-B	G1/8	3	15	25,5	12	4,7	20,8	13
VASB-30-...-PUR-B	G1/8	3	30	34	12	4,7	29,3	13
VASB-40-...-PUR-B	G1/4	4	40	43	17	5,8	37,2	17
VASB-55-...-PUR-B	G1/4	4	55	52	17	5,8	46,2	17
VASB-75-...-PUR-B	G1/4	4	75	43,5	17	5,8	37,7	17
VASB-100-...-PUR-B	G1/4	4	100	43,5	17	5,8	37,7	17
VASB-125-...-PUR-B	G3/8	7	125	60	20	6	54	19

Ordering data

Ordering data – Suction cup with connector VAS-...-S-PUR-B, vacuum connection on the side

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364-A1-L	4 g	8025969	VAS-8-M5-S-PUR-B

Ordering data – Suction cup with connector VAS-...-NBR

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	2 mm	M3	VDMA24364-A1-L	1 g	173438	VAS-2-M3-NBR
	5 mm	M5		2 g	173439	VAS-5-M5-NBR
	10 mm			3 g	173440	VAS-10-M5-NBR
	75 mm	G1/4		76 g	36145	VAS-75-1/4-NBR
	100 mm			138 g	34586	VAS-100-1/4-NBR
	125 mm	G3/8		152 g	152605	VAS-125-3/8-NBR

Suction cup with connection VAS-...-NBR-F1A (for battery production)

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364-A1/A2-L	1.5 g	8204239	VAS-8-M5-NBR-F1A
	15 mm	G1/8		3.8 g	8204259	VAS-15-1/8-NBR-F1A
	30 mm			5.3 g	8204260	VAS-30-1/8-NBR-F1A
	40 mm	G1/4		13.7 g	8204304	VAS-40-1/4-NBR-F1A
	55 mm			18.5 g	8204305	VAS-55-1/4-NBR-F1A

Dimensions – Suction cup VAS-...-SI-B

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364 zone III	2 g	1377781	VAS-8-M5-SI-B
	10 mm				1385610	VAS-10-M5-SI-B
	15 mm	G1/8		4 g	1376604	VAS-15-1/8-SI-B
	30 mm			5 g	1377752	VAS-30-1/8-SI-B
	40 mm	G1/4		14 g	1379454	VAS-40-1/4-SI-B
	55 mm			19 g	1379348	VAS-55-1/4-SI-B
	75 mm			62 g	1382165	VAS-75-1/4-SI-B
	100 mm			116 g	1386376	VAS-100-1/4-SI-B
	125 mm	G3/8		214 g	1415120	VAS-125-3/8-SI-B

Dimensions – Suction cup with connector VAS-...-PUR-B

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364-A1-L	4 g	1396086	VAS-8-M5-PUR-B
	10 mm				1469698	VAS-10-M5-PUR-B
	15 mm	G1/8		11 g	1396087	VAS-15-1/8-PUR-B
	30 mm			12 g	1396090	VAS-30-1/8-PUR-B
	40 mm	G1/4		26 g	1396092	VAS-40-1/4-PUR-B
	55 mm			30 g	1396095	VAS-55-1/4-PUR-B
	75 mm			77 g	1396096	VAS-75-1/4-PUR-B

Ordering data

Dimensions – Suction cup with connector VAS-...-PUR-B

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	100 mm	G1/4	VDMA24364-A1-L	140 g	1396098	VAS-100-1/4-PUR-B
	125 mm	G3/8		249 g	1396108	VAS-125-3/8-PUR-B

Ordering data – Suction cup with connector VASB-...-NBR, protective bellows

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	75 mm	G1/4	VDMA24364-A1-L	95 g	35415	VASB-75-1/4-NBR
	100 mm		VDMA24364-B1/B2-L		35416	VASB-100-1/4-NBR
	125 mm	G3/8	VDMA24364-A1-L	207 g	152609	VASB-125-3/8-NBR

Suction cup with connection VASB-...-NBR-F1A, protective bellows (for battery production)

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364-A1/A2-L	1.5 g	8204343	VASB-8-M5-NBR-F1A
	15 mm	G1/8		4.1 g	8204344	VASB-15-1/8-NBR-F1A
	30 mm			7 g	8204432	VASB-30-1/8-NBR-F1A
	40 mm	G1/4		17.1 g	8204433	VASB-40-1/4-NBR-F1A
	55 mm			26.9 g	8204438	VASB-55-1/4-NBR-F1A

Dimensions – Suction cup VASB-...-SI-B, protective bellows

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364 zone III	4 g	1394696	VASB-8-M5-SI-B
	15 mm	G1/8			1377689	VASB-15-1/8-SI-B
	30 mm			7 g	1377637	VASB-30-1/8-SI-B
	40 mm	G1/4		18 g	1372910	VASB-40-1/4-SI-B
	55 mm			29 g	1373812	VASB-55-1/4-SI-B
	75 mm			78 g	1378427	VASB-75-1/4-SI-B
	100 mm			132 g	1382277	VASB-100-1/4-SI-B
	125 mm	G3/8		247 g	1387375	VASB-125-3/8-SI-B

Dimensions – Vacuum cup VASB-...PUR-B, bellows

	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	8 mm	M5	VDMA24364-A1-L	4 g	1395637	VASB-8-M5-PUR-B


Ordering data

Dimensions – Vacuum cup VASB-...PUR-B, bellows						
	Suction cup diameter	Vacuum connection	LABS (PWIS) conformity	Product weight	Part no.	Type
	15 mm	G1/8	VDMA24364-A1-L	11 g	1395671	VASB-15-1/8-PUR-B
	30 mm	G1/4		14 g	1395690	VASB-30-1/8-PUR-B
	40 mm			30 g	1395691	VASB-40-1/4-PUR-B
	55 mm			39 g	1396063	VASB-55-1/4-PUR-B
	75 mm			90 g	1396064	VASB-75-1/4-PUR-B
	100 mm			155 g	1396066	VASB-100-1/4-PUR-B
	125 mm			294 g	1396067	VASB-125-3/8-PUR-B
		G3/8				

Accessories

Adapter AD				
	Short type code	LABS (PWIS) conformity	Part no.	Type
	AD	VDMA24364-B1/B2-L	160256	AD-M12X1,25-1/4
			157329	AD-M6-1/8
			157334	AD-M10X1,25-1/4
			157332	AD-M8-1/4
			157330	AD-M6-1/4
			160257	AD-M12X1,25-3/8
			157333	AD-M10X1,25-1/8
			157331	AD-M8-1/8
			157328	AD-M6-M5

Vacuum security valve ISV						
	Size	LABS (PWIS) conformity	Suitability for the production of Li-ion batteries	Product weight	Part no.	Type
	G1/8	VDMA24364-B1/B2-L	F1a	9 g	8217204	ISV-1/8-F1A
	G1/4			16 g	8217205	ISV-1/4-F1A
	G3/8	VDMA24364-B2-L		33 g	33971	ISV-3/8
	M5	VDMA24364-B1/B2-L	F1a	4 g	8217206	ISV-M5-F1A

Length compensator VAL						
	Vacuum connection	Design	Suitability for the production of Li-ion batteries	Product weight	Part no.	Type
	Female thread G1/8	Vacuum port on top	F1a	62 g	8214723	VAL-1/8-10-F1A
	Female thread G1/4			118 g	8214724	VAL-1/4-20-F1A
	Female thread G3/8			275 g	8210510	VAL-3/8-80-F1A
	Female thread M5			25 g	8214722	VAL-M5-5-F1A