

Electric cylinder EPRF-BS-75-200-10P-F-M1

Part number: 8211892

FESTO



 General operating condition

Data sheet

Feature	Value
Size	75
Stroke	200 mm
Stroke reserve	0 mm
Piston rod thread	M10
Reversing backlash theoretical	<100 µm
Spindle diameter	25 mm
Spindle pitch	10 mm/U
Torsional backlash at piston rod +/-	0.5 deg
Mounting position	Any
Piston-rod end	Female thread
Type of motor	Servo motor
Position detection	None
Design	Electric cylinder with ball screw
Spindle type	Ball screw
Symbol	00991941
Protection against torque/guide	With plain-bearing guide
Max. drive speed	3000 rpm
Max. acceleration	15 m/s ²
Max. speed	500 m/s
Max. homing speed	0.01 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 60 °C
Suitable for use with food	See declaration of conformity
Relative air humidity	0 - 95% Non-condensing
Degree of protection	IP69K
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	0.15 J
Max. drive torque	13.25 Nm
Max. moment Mx	0 Nm

Feature	Value
Max. moment My	31.2 Nm
Max. moment Mz	31.2 Nm
Max. radial force at drive shaft	700 N
Max. feed force Fx	7500 N
Frictional torque independent of load	0.516 Nm
Reference value effective load, horizontal	600 kg
Reference value effective load, vertical	300 kg
Mass moment of inertia JH per metre of stroke	2.2453 kgcm ²
Mass moment of inertia JL per kg of working load	0.0253 kgcm ²
Mass moment of inertia JO	0.5098 kgcm ²
Reference service life	5000 km
Maintenance interval	Lifetime lubrication
Moving mass for 0 mm stroke	1267 g
Additional moving mass per 10 mm stroke	15.1 g
Basic weight for 0 mm stroke	4881 g
Additional weight per 10 mm stroke	84.5 g
Type of mounting	With female thread
Note on materials	RoHS compliant
Material cover cap	High-alloy stainless steel
Material cover	High-alloy stainless steel
Material seals	TPE-U(PU)
Material dynamic seals	TPE-U(PU)
Material housing	High-alloy stainless steel
Material piston rod	High-alloy stainless steel
Material ball screw nut	Steel
Material spindle	Bearing steel
Material cylinder barrel	High-alloy stainless steel